


IEC connectors

Order code	Manufacturer code	Description
23-0107	PX0597	IEC CBL SOCKET - HOT CONDITION

IEC connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

IEC Cable Socket – Hot Condition




Rewireable cable socket which mates with hot condition inlets.
Fitted with cable strain relief, and internal screw terminals.

Approvals :
UL, CSA, VDE, BS, SEMKO and DEMKO

Specifications

Terminations:	Screw Terminals
Max. Rating:	10A. 250V a.c.
Contact Resistance:	<10mΩ
Insulation Resistance:	>10 ³ MΩ
A.C. Breakdown:	Pole-Pole 4.5kV. Poles-Accessible Parts 4kV.
Operating Temp. Range:	-40°C to +70°C
Withdrawal Force:	10N (Min). 50N (Max).
Mouldings:	Nylon, Flammability Rating UL94V-0
Contacts:	Brass: Clean.
Mating Connectors:	PX0590, PX0595



Bulgin Type	Description
PX0597	IEC Socket - Hot