


NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3604
2. TEFLON MIL-P-19488
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70  $\mu$ " THICK OVER COPPER STRIKE
6. GOLD PL 1-3 $\mu$ " OVER NICKEL PL 70  $\mu$ " THICK OVER COPPER STRIKE

8	Washer	Steel	Nickel
7	Braid Clamp	Brass	Silver
6	Nut	Brass	Nickel
5	Gasket	Rubber	Red
4	Shell	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish



DIMENSIONS ARE IN MILLIMETERS

252530

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED

TOLERANCES  
 0.5-6=±0.2  
 6-30=±0.4  
 30-120=±0.6  
 120-315=±1.0  
 315-1000=±1.6  
 1000-2000=±2.4

PART NO.

0404013

TITLE: N CLAMP PLUG RIGHT ANGLE TYPE FOR  
 RG213/U CABLE

DATE

July / 27 / 2010

NOT SCALED DRAWING

DRAWING NO.