


BZV01/Z0000/02 Datasheet

**Product Name // Vertical Power Entry Module 58.9mm C14
Cold Condition Inlet Integral Single Fused (PF0011) 6.3mm
Tab Termination Unfiltered Single Contact Illuminated
Switch Red**

 [View Product Page](#)



BZV01/*****/** } A = 59.7 With Filter
 BZV02/*****/** } A = 27.4 Without Filter
 BZV15/*****/** } A = 59.7 With Filter
 BZV16/*****/** } A = 37.9 Without Filter
 Panel Thickness. 1.0, 1.5, 2.0, 3.0mm.

// Product Description:

- ⊕ Vertical Power Entry Module 58.9mm/72.3mm
- ⊕ C14 Cold Condition Inlet with integral fuseholder(s) depending on part code:
- ⊕ Part codes prefixed BZV01, BZV02: PF0011 Single Fused Inlet
- ⊕ Part codes prefixed BZV15, BZV16: PF0033 Twin Fused Inlet
- ⊕ Choice of Termination depending on part code:
- ⊕ Part codes prefixed BZV01, BZV15: 6.3mm Tab
- ⊕ Part codes prefixed BZV02, BZV16: 2.8mm Tab
- ⊕ Choice of mains filter depending on part code:
- ⊕ Part codes containing /Z0000 are unfiltered
- ⊕ Choice of mains filter options (part codes containing codes starting /A)
- ⊕ Choice of many other options as specified by individual part code, including indicators, illuminated switches, switch markings, etc

// General Information:

Product Display Title:	Vertical Power Entry Module 58.9mm/72.3mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	10A
Filter Type:	Unfiltered
Function:	C14 Inlets
Fuseholder Inlet Type:	Integral Single Fused
iec Connector Components:	None
iec Connector Mates With:	PF0011
iec Filter Options:	Unfiltered
iec Neon Colour:	Red
iec Vertical Module Height:	58.9mm
Inlet Type:	C14 Cold Condition Inlet
Rohs Compliant:	Yes
Switch Type:	Single Contact Illuminated
Voltage Max:	250V

// Product PDF Links

 [Power Entry Modules product data](#)

// Product 3D CAD Model Links

 [BZV01/Z0000/023D CAD Model](#)