



Datasheet

Item no. 1586522

V1_0617_02_EN



NOTES:

Mechanical:

1. Housing material : Glass Filled Polyester UL94V-0 ,
Color: Black
2. Contact material: Phosphor Bronze $t=0.35\text{mm}$
3. Contact plating: 6u" Gold on contact plating
100~200u" Tin on solder area
all over 30~50u" Nickel
4. Operating Life: 750 Cycles min.
5. PCB Retention Pre-solder: 1 LB min.
6. PCB Retention Post-solder: 10 LBS min.



Electrical:

1. Voltage Rating: 125VAC.
2. Current Rating: 1.5AMP.
3. Contact Resistance: 50mΩ max.
4. Insulation Resistance: 1000MΩ min. @ 500 VDC
5. Dielectric Strength: 1000 VAC 60Hz, 1 min.

Environmental:

1. Storage: -40°C To +85°C
2. Operation: -40°C~+85°C
3. Wave Soldering Temp: 200~220°C(5~10S)

Packing: 90pcs/Tray, 3600pcs/Carton



PC Board Layout
Component Side Shown
PC Board For T=1.60mm

RoHS compliant
Unit:mm



File No.: E345352