





Datasheet

Item no. 1586529

V1_0617_02_EN



Frequency	Near-End Cross Talk dB, MIN.	Return Loss dB, MIN.
1.0 MHZ	65.0	23.0
4.0 MHZ	65.0	23.0
8.0 MHZ	62.0	23.0
10.0 MHZ	60.0	23.0
16.0 MHZ	56.0	23.0
20.0 MHZ	54.0	23.0
25.0 MHZ	52.0	14.0
31.25 MHZ	50.0	14.0
62.5 MHZ	44.0	14.0
100.0 MHZ	40.0	14.0

NOTES:

Mechanical:

- Housing material : PBT UL94V-0
Color: Black
- Contact material: Phosphor Bronze t=0.35mm
- Contact plating: 6u" Gold on contact are
100~200u" Tin on solder area
all over 30~50u" Nickel
- Operating Life: 750 Cycles min.
- PCB Retention Pre-solder: 1 LB min.
- PCB Retention Post-solder: 10 LBS min.


Electrical:

- Voltage Rating: 125VAC.
- Current Rating: 1.5AMP.
- Contact Resistance: 30mΩ max.
- Insulation Resistance: 1000 MΩ min. @ 500 VDC
- Dielectric Strength: 1000 VAC 60Hz, 1 min.


Environmental:

- Storage: -40°C To +85°C
- Operation: -40°C~+85°C
- Wave Soldering Temp: 200~220°C(5~10S)

Packing: 100pcs/Tray, 3200pcs/Carton



Detail A
2 : 1



PC Board Layout
Component Side Shown



File No.: E345352

RoHS compliant
Unit:mm