

## 32mm fuses

Order code	Manufacturer code	Description
26-5640	n/a	1A ULTRA RAPID 32X6.3MM FUSE
26-5642	n/a	1.6A ULTRA RAPID 32X6.3MM FUSE
26-5644	n/a	2A ULTRA RAPID 32X6.3MM FUSE
26-5646	n/a	3.15A ULTRA RAPID 32X6.3MM FUSE
26-5648	n/a	5A ULTRA RAPID 32X6.3MM FUSE
26-5650	n/a	6.3A ULTRA RAPID 32X6.3MM FUSE
26-5652	n/a	8A ULTRA RAPID 32X6.3MM FUSE
26-5654	n/a	10A ULTRA RAPID 32X6.3MM FUSE
26-5656	n/a	12.5A ULTRA RAPID 32X6.3MM FUSE
26-5658	n/a	16A ULTRA RAPID 32X6.3MM FUSE

32mm fuses	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

## Fuses & Circuit Breakers

### Ultra Rapid 32x 6.3mm Ceramic Fuse

Order Code	Manufacturers Code	Description
26-5640	70-125-40/1A	1A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5642	70-125-40/1.6A	1.6A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5644	70-125-40/2A	2A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5646	70-125-40/3.15A	3.15A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5648	70-125-40/5A	5A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5650	70-125-40/6.3A	6.3A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5652	70-125-40/8A	8A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5654	70-125-40/10A	10A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5656	70-125-40/12.5A	12.5A Ultra Rapid 32x 6.3mm Ceramic Fuse
26-5658	70-125-40/16A	16A Ultra Rapid 32x 6.3mm Ceramic Fuse

**JFHR2** **June 19, 1996**  
**Component - Fuses, Special Purpose**

**SIBA SICHERUNGEN-BAU GMBH**  
**POSTFACH 1940 , 44509 LUNEN FED REP**  
**GERMANY**

**E180276 (N)**  
 (A card)

Semiconductor fuses, Cat. No. 20 282 (Size 00C) followed by two numbers, followed by ampere rating, rated 700 Vac, 35-315A; Cat. No. 20 189 (Size 00) followed by two numbers, followed by ampere rating, rated 700 Vac, 160-355A.

Cat. No. 80 033 06 followed by ampere rating, rated 600 Vac, 5-30A.

Cat. No. 70 001 40 followed by ampere rating, rated 250 Vac, 125mA-5A; Cat. No. 70 007 40 followed by ampere rating, rated 250 Vac, 6.3-12.5A.

Cat. No. 50 179 08 followed by ampere rating, rated 700 Vac, 1-30A.

Cat. No. 50 124 06 followed by ampere rating, rated 700 Vac, 6-40A.

Cat. No. 50 140 08 followed by ampere rating, rated 700 Vac, 6-100A.

Cat. No. 70 066 65 followed by ampere rating, rated 500 Vac, 500mA-2.5A.

Cat. No. 70 125 40 followed by ampere rating, 160mA-2A rated 700 Vac; 2.5A-20A rated 500 Vac.

Reports: May 23, 1995; May 23, 1995; April 16, 1996; April 16, 1996; April 17, 1996; April 18, 1996; June 20, 1996; June 21, 1996.

(Cont. on B card)

D11/0276748

129263001

**Underwriters Laboratories Inc.®**