


## Specifications

Nominal voltage		1.2V		
Capacity (mAh)		C/5	C	
	Nominal	5000	4500	
	Typical	5250	5000	
Diameter		1.28 ± 0.02 in 32.5 ± 0.5 mm		
Height		2.38 ± 0.02 in 60.5 ± 0.5 mm		
Weight		165g		
Internal impedance at 1000Hz.		12 mΩ (After charge)		
Charge	Standard	500mA × 14hrs.		
	Normal	1000mA × 7hrs.		
	Trickle	Max.	250mA	
		Min.	167mA	
Ambient temperature	Charge	Standard	-20°C ~ 30°C	
		Normal	0°C ~ 45°C	
	Discharge	-20°C ~ 50°C		
		Storage	-20°C ~ 35°C	

### Note

1. Nominal capacity, rated at C/5, 20°C.
2. Other capacities are for reference.
3. Weight and internal impedance are for reference.



## Typical characteristics

