


Impedance	Non-constant
Frequency range	0-300 MHz
Voltage rating	500 volts peak
Temperature range	Teflon insulations: -65° C to 165° C
Mating	5/8-24 UNEF threaded coupling

Recommended  
Cable Stripping



No	Description	Material	Finish
4	Shell	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel

- NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BODY/CONTACT: BRASS PER JIS-C3804
  2. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
  3. CONNECTOR INTERFACE PER MIL-STD-348A
  4. PART TO BE CLEAN AND FREE BURRS
  5. NICKEL PL. 70 μ" THICK OVER COPPER STRIKE
  6. GOLD PL 1-Su" OVER NICKEL PL. 70 μ" THICK OVER COPPER STRIKE

DIMENSIONS ARE IN MILLIMETERS		<b>251283</b>		RoHS COMPLIANT	
UNLESS OTHERWISE SPECIFIED TOLERANCES	0.5-6= ±0.2	PART NO.	<b>0406043</b>		TITLE: UHF TWIST-ON PLUG FOR AIRCELL7 CABLE
	6-30= ±0.4	DATE	July / 29 / 2010		
	30-120= ±0.6	NOT SCALED DRAWING			DRAWING NO.
	120-315= ±1.0				
	315-1000= ±1.6				
	1000-2000= ±2.4				