

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bus connector to connect BC modules on the DIN rail; suitable for BC DEV-KITS, contains HBUS 107,6 and pin strip



Your advantages

- Space-saving installation under the housing in the DIN rail
- Fast module-to-module communication without additional wiring effort
- One DIN rail connector for each overall width

Commercial data

Item number	2202545
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ACHBAD
GTIN	4055626142456
Weight per piece (including packing)	29.3 g
Weight per piece (excluding packing)	27.5 g
Customs tariff number	85369010
Country of origin	DE

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Set consists of

HBUS 107,6-16P-1S BK - DIN rail bus connectors

2896306

<https://www.phoenixcontact.com/pc/products/2896306>



DIN rail connector, color: black, nominal current: 3 A (Total current of 25 A max.), rated voltage (III/2): 30 V, number of positions: 16, product range: BC 107,6..., pitch: 2.54 mm, mounting: DIN rail mounting, locking: without

PSTD 0,65X0,65/9-2,54 - Pin strip

2200700

<https://www.phoenixcontact.com/pc/products/2200700>



Pin strip, color: black, contact connection type: Pin, number of potentials: 18, number of rows: 2, number of positions: 18, number of connections: 18, product range: PSTD 0,65X0,65/...-V, pitch: 2.54 mm, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 2.5 mm, locking: without, type of packaging: packed in cardboard

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Technical data

Product properties

Product type	DIN rail connector
Product family	BC 107,6..
Number of positions	16
Pitch	2.54 mm

Data management status

Article revision	02
------------------	----

Electrical properties

Nominal current I_N	3 A (Total current of 25 A max.)
Contact resistance	23.9 m Ω
Rated voltage (III/3)	30 V
Rated surge voltage (III/3)	0.8 kV
Rated voltage (III/2)	30 V
Rated surge voltage (III/2)	0.8 kV
Rated voltage (II/2)	100 V
Rated surge voltage (II/2)	0.8 kV

Material specifications

Material data - contact

Contact material	Cu alloy
Surface characteristics	Completely gold-plated

Material data - housing

Color (Housing)	black (9005)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0

material specifications - connector

Color ()	()
----------	----

Dimensions

Pitch	2.54 mm
Width [w]	107.6 mm

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Mechanical tests

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	20 m/s ²
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis (pos. and neg.)

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	0.91 kV
Contact resistance R ₁	23.9 mΩ
Contact resistance R ₂	24 mΩ
Insertion/withdrawal cycles	25

Climatic test

Specification	DIN 50018:2013-05
Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	0.55 kV

Glow-wire test

Specification	IEC 60695-2-10:2013-04
Temperature	850 °C
Time of exposure	30 s

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	150 m/s ²
Shock duration	11 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 55 °C

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Relative humidity (storage/transport)	80 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Electrical tests

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Insulating material group	I
Rated insulation voltage (III/3)	30 V
Rated surge voltage (III/3)	0.8 kV
minimum clearance value - non-homogenous field (III/3)	0.8 mm
minimum creepage distance (III/3)	1.3 mm
Rated insulation voltage (III/2)	30 V
Rated surge voltage (III/2)	0.8 kV
minimum clearance value - non-homogenous field (III/2)	0.2 mm
minimum creepage distance (III/2)	0.53 mm
Rated insulation voltage (II/2)	100 V
Rated surge voltage (II/2)	0.8 kV
minimum clearance value - non-homogenous field (II/2)	0.2 mm
minimum creepage distance (II/2)	0.71 mm

Packaging specifications

Outer packaging type	Carton
----------------------	--------

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Classifications

ECLASS

ECLASS-11.0	27460202
ECLASS-12.0	27460202
ECLASS-13.0	27460202

ETIM

ETIM 9.0	EC002638
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HBUS 107,6-16P-1S DEV-KIT BK - DIN rail bus connectors



2202545

<https://www.phoenixcontact.com/pc/products/2202545>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com