

## NSYS3D8625P

Spacial S3D plain door with mount.plate.  
H800xW600xD250.IP66 IK10 RAL7035.



### Main

Range	Spacial
Product name	Spacial S3D
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	800 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	250 mm
Door type	Plain
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	Body 1 Mounting plate 1 Door with lock 1 Cable gland plate 1

### Complementary

Variant particularity	Gutter-shaped front rail double sheet thickness Single piece body
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 points lock, 3 mm double-bar
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Galvanised steel for mounting plate Steel for enclosure
Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure :
Standards	IEC 62208
Product certifications	BV CUL DNV GL LR UL

### Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------