

# NSYSDF168

Spacial SD Control desk with console -  
H1400xW1600xD845 - IP55



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial SD  |
| Device application          | Multi-purpose   |
| Product or component type   | Control desk with console and desk  |
| Enclosure nominal height    | 1400 mm   |
| Enclosure nominal width     | 1600 mm   |
| Enclosure nominal depth     | 845 mm  |
| Installation accessory type | Floor-standing  |
| Device composition          | Cable gland plate 1<br>Structure 1<br>Adjustment rail 4<br>Pneumatic stay 2 desk lid<br>Front console door 1<br>Desk lid 1<br>Mechanical stay 2 front console door<br>Lock 6 front door<br>Handle lock 1 rear door<br>Front door 2<br>Rear door 2 |

## Complementary

|                             |   |
|-----------------------------|---|
| Body type                   | Single piece structure folded and welded  |
| Door type                   | Plain   |
| Number of doors             | 2 front<br>2 rear   |
| Door opening side           | Reversible 120 ° front and rear doors<br>Folding 75 ° desk lid and console cover  |
| Lock type                   | 2 points lock, 3 mm double-bar<br>Handle lock, 5 mm double bar  |
| Mounting plate description  | Without mounting plate  |
| Type of gland plate         | 1 entry plate   |
| Accessibility for operation | Front<br>Rear   |
| Removable parts             | Desk lid by hinges<br>Cable gland plate by clipping screws<br>Front door by hinges<br>Front console door by hinges<br>Rear door by hinges |
| Material                    | Steel body  |
| Surface finish              | Epoxy-polyester powder  |
| Thickness                   | 1.5 mm  |

## Environment

|                         |                |
|-------------------------|----------------|
| standards               | IEC 62208      |
| IP degree of protection | IP55 IEC 60529 |
| IK degree of protection | IK10 IEC 62262 |

## Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| RoHS (date code: YYWW)   | Compliant - since 0940 - Schneider Electric declaration of conformity |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                                  |   |
|----------------------------------|---|
| REACH                            | Reference not containing SVHC above the threshold |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations             |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|