

NSYSF20680M

Spacial SF compartmentalised enclosure - assembled - 2000x600x800 mm



Main

Range	Spacial
Product name	Spacial SFM
Device application	Compartmentalised application
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	800 mm
Enclosure mounting	Floor-standing
Product specific application	Insulating the control of a device Reduce the destructive effects of a short-circuit
Device composition	1 rear panel 1 roof 1 structure 2 intermediate crossbars 2 panels for modularity for top and bottom

Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front Rear Sides of enclosure
Removable parts	Rear panel fixed by screws Roof fixed by screws
Material	Galvanised steel for frame Galvanised steel for uprights Sheet steel for panels Zamak for hinge
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035

Environment

standards	IEC 62208
-----------	-----------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1541 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.