

NSYSMX201040H

SMX 316L stainless monobloc enclosure,
H2000xW1000xD400mm, Scotch Brite® finish.



Main

| | |
|-----------------------------|--|
| Range | Spacial |
| Product name | Spacial SMX |
| Device application | Multi-purpose |
| Product or component type | Compact enclosure |
| Enclosure nominal height | 2000 mm |
| Enclosure nominal width | 1000 mm |
| Enclosure nominal depth | 400 mm |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 1 cable gland plate 4 mounting plate bracket 2 door 1 locking system with handle (door) |

Complementary

| | |
|-----------------------------|--|
| Body type | Single piece body folded and welded |
| Door type | Plain |
| Number of doors | Front face: 2 door(s) |
| Door opening side | 120 °, reversible |
| Lock type | 3 points lock, handle with 5 mm double-bar insert |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Plain |
| Accessibility for operation | Front |
| Removable parts | Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips |
| Material | Handle: zamak Hinge: stainless steel Body and door: stainless steel 316L |
| Surface finish | Enclosure: Scotch-Brite® brushed Handle: painted |
| Thickness | 1.5 mm |

Environment

| | |
|------------------------------|-------------------------------|
| standards | IEC 62208 |
| product certifications | UL 508 CAN/CSA 22 |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| environmental characteristic | Corrosive Specific hygiene |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
