

Distribution Boxes



Technical Datasheet

Key Features

- High Thermal Stability - ASA Plastic
- Transparent Polycarbonate Door
- UV Stable / Halogen Free
- Internal Terminal Busbar Current Rating 63A
- Rated Insulation Voltage 1500VDC
- IP65 Rating - Inside / Outside Use
- Earth & Neutral Bars Included
- Suitable for Photovoltaic Applications
- Key Accessory



Each enclosure comes with a set of accessories:-

- 6-way divisible blanking plates
- 4 x wall plugs and screws
- 4 x internal screw caps
- Application identifier stickers



Options & Ordering Codes

E - 04W	
Series	
Distribution Boxes	E
Modules / Poles	
4-Way	04W
8-Way	08W
12-Way	12W
24-Way	24W
36-Way	36W

Technical Data

Protection Class	IP65
Isolation Class	II
Impact Kit	IK07
Normal Voltage	400V AC
Rated Insulation Voltage	1500VDC
Temperature Range	-20°C to 60°C
Colour	RAL 7035
IEC Capability	60670-24

Specification

Type	Description	No. of Terminals PE/N	Dimensions - mm (H x W x D)	Entries Description
E-04W	4 Modules (1 x DIN Rail row)	4/4	200 x 127 x 120	4 x M20 + 4 x M25/32
E-08W	8 Modules (1 x DIN Rail row)	8/8	200 x 200 x 120	8 x M20 + 6 x M25/32
E-12W	12 Modules (1 x DIN Rail row)	10/10	258 x 318 x 142	12 x M20 + 10 x M25/32 + 4 x M32/M40 + 2 x Knockout Plate 37 x 90mm
E-24W	24 Modules (2 x DIN Rail row)	13/13	383 x 318 x 142	12 x M20 + 10 x M25/32 + 4 x M32/M40 + 2 x Knockout Plate 37 x 90mm
E-36W	36 Modules (3 x DIN Rail row)	15/15	507 x 318 x 142	12 x M20 + 10 x M25/32 + 4 x M32/M40 + 6 x Knockout Plate 37 x 90mm

Accessories

Type	Description
E-LOCK	Enclosure Key Lock

