



KEB-1025



Die profile



Crimp profile

KEB-1025 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on endsplices/ferrules terminals on wires ranging from 10,0-25,0 mm².

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information See instruction sheet.

- Professional crimp tool for optimized crimp performance.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

Technical data

Lenght :	255 mm/10,04"
Height :	72 mm/2,83"
Weight :	560 gr/1,23 lbs
Connector:	Endsplices/Ferrules
Description:	Insulated and Uninsulated
Wire size awg:	6-4 AWG
Wire size mm ² :	10,0-25,0 mm ² / 6-4 AWG

Distributors address info