

Electronic housing - BC 107,6 DEV-KIT KMGY - 2202525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DEV-KIT BC 107,6: contains 1 x BC 107,6 housing and PCB terminal blocks (MKDS), supplied in individual parts

Why buy this product

- ✓ Standard-compliant housing according to DIN 43880 with overall width of 107,6 mm
- ✓ PCB terminal blocks with 5 mm pitch, conductor cross section 1.5 mm²
- ✓ Optional hole matrix PCB for soldering THT components by hand
- ✓ Connection of individual housing modules with each other by means of the optional HBUS via DIN rail

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141756
Weight per Piece (excluding packing)	172.5 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ACHIBA

Technical data

General

Housing type	Component housing
Housing material	Polycarbonate
Color	light gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	89.7 mm
Constructional height	62.2 mm
Width	107.6 mm

Technical data

Flammability rating according to UL 94	V0
--	----

Electronic housing - BC 107,6 DEV-KIT KMGY - 2202525

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Additional products

PCB - BC 107,6/40 U11 HBUS DEV-PCB - 2202544



Printed-circuit board for the BC 107,6 DEV-KIT

Plug - HBUS 107,6-16P-1S DEV-KIT BK - 2202545

Bus connector to connect BC modules on the DIN rail; suitable for BC DEV-KITS, contains HBUS 107,6 and pin strip

