

UM-BASIC 108 100MM DEV-KIT KMGY - Housing set



2202528

<https://www.phoenixcontact.com/pc/products/2202528>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DEV-KIT UM-BASIC: contains 1 x UM-BASIC 100MM profile housing and PCB terminal blocks (SMKDS), supplied in individual parts



Your advantages

- Different base profiles, each with three PCB levels
- Module covers of different geometries can be positioned in any way
- Compatibility with many standard connection technologies
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2202528
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ACHDAD
GTIN	4055626141787
Weight per piece (including packing)	186.4 g
Weight per piece (excluding packing)	184.4 g
Customs tariff number	85369010
Country of origin	DE

UM-BASIC 108 100MM DEV-KIT KMGY - Housing set



2202528

<https://www.phoenixcontact.com/pc/products/2202528>

Set consists of

UM-BASIC/PRO 108 COVER-L KMGY - Lateral element

2202021

<https://www.phoenixcontact.com/pc/products/2202021>

Lateral element (left) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 108 mm



UM-BASIC/PRO 108 COVER-R KMGY - Lateral element

2202022

<https://www.phoenixcontact.com/pc/products/2202022>

Lateral element (right) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 108 mm



UM-BASIC 108 100MM DEV-KIT KMGY - Housing set



2202528

<https://www.phoenixcontact.com/pc/products/2202528>

SMKDS 2,5/ 8-5,08 - PCB terminal block

1736845

<https://www.phoenixcontact.com/pc/products/1736845>



PCB terminal block, nominal current: 20 A, rated voltage (III/2): 400 V, nominal cross section: 2.5 mm², number of potentials: 8, number of rows: 1, number of positions per row: 8, product range: SMKDS 2,5, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, mounting: Wave soldering, conductor/PCB connection direction: 50 °, color: green, Pin layout: Linear pinning, Solder pin [P]: 3.5 mm, number of solder pins per potential: 1, type of packaging: packed in cardboard

UM-BASIC PROFILE - Profile

2200149

<https://www.phoenixcontact.com/pc/products/2200149>



Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile length (configurable): 3 cm ... 200 cm, depth: 19.8 mm, Note: required profile length = PCB length - 16.2 mm

Technical data

Notes

Assembly note	Please observe the assembly instructions available in the download area.
---------------	--

Product properties

Product type	Stackable housing set
Housing type	Press-drawn section housings
Housing series	UM-BASIC
Type	incl. 2 lateral elements
Ventilation openings present	no

Dimensions

Width	104 mm
Height	127.8 mm
Depth from top edge of DIN rail	32.45 mm
Dimensions	108 mm x 100 mm (PCB dimensions)

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Insulating material	PVC
Housing material	PVC / PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 50 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Relative humidity (storage/transport)	95 %

PCB data

Number of PCB holders	3
Type of PCB mount	Insertion/securing with additional elements
Total PCB surface	8630 mm ²
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UM-BASIC 108 100MM DEV-KIT KMGY - Housing set



2202528

<https://www.phoenixcontact.com/pc/products/2202528>

Mounting position	parallel to the DIN rail
-------------------	--------------------------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-BASIC 108 100MM DEV-KIT KMGY - Housing set



2202528

<https://www.phoenixcontact.com/pc/products/2202528>

Classifications

ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190301

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

2202528

<https://www.phoenixcontact.com/pc/products/2202528>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com