

3IN1 LEMON CLEANER SANITISER

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 08/11/2016

Revision date: 05/06/2015

Version: 10.0

3IN1 LEMON CLEANER SANITISER

33-120

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : 3IN1 LEMON CLEANER SANITISER
Product code : 33-120
Type of product : Technical product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Industrial/Professional use spec : For professional use only
Use of the substance/mixture : Hard Surface Cleaner/Sanitiser

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

ARROW COUNTY SUPPLIES
ARROW HOUSE, LONGDEN ROAD, SHREWSBURY, SY3 9AE, UNITED KINGDOM
Tel: 01743 283600 Fax: 01743 283601 Email: purchasing@arrowcounty.com

1.4. Emergency telephone number

Emergency number : Mon to Fri 8.30am to 5.00pm - 01743 283600

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Eye Irrit. 2 H319

Full text of H-phrases: see section 16

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) :

Warning

Hazard statements (CLP) :

H319 - Causes serious eye irritation

Precautionary statements (CLP) :

P264 - Wash hands thoroughly after handling
P280 - Wear eye protection
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P337+P313 - If eye irritation persists: Get medical advice/attention

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	Classification according to Directive 67/548/EEC	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Cocamidopropyl betaine	(CAS No) 147170-44-3	1 - 5	Xi; R41	Eye Dam. 1, H318 Aquatic Chronic 3, H412

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Name	Product identifier	%	Classification according to Directive 67/548/EEC	Classification according to Regulation (EC) No. 1272/2008 [CLP]
N,N-dimethyltetradecylamine N-oxide	(CAS No) 3332-27-2 (EC no) 222-059-3 (REACH-no) 01-2119949262-37	1 - 5	Xi; R41 Xi; R38 N; R50	Skin Irrit. 2, H315 Eye Dam. 1, H318

Full text of R- and H-phrases: see section 16

SECTION 4: First aid measures**4.1. Description of first aid measures**

First-aid measures general	: Get medical advice/attention if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash with plenty of soap and water.
First-aid measures after eye contact	: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Give nothing or a little water to drink. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries after inhalation	: May cause respiratory irritation.
Symptoms/injuries after skin contact	: Repeated exposure may cause skin dryness or cracking.
Symptoms/injuries after eye contact	: Causes eye irritation.
Symptoms/injuries after ingestion	: May cause a light irritation of the linings of the mouth, throat, and gastrointestinal tract.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable extinguishing media : Carbon dioxide. Dry powder. Foam.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

No additional information available

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures****6.1.1. For non-emergency personnel**

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Use personal protective equipment as required.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Collect spillage.

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Precautions for safe handling : Avoid contact with eyes.

Hygiene measures : Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Does not require any specific or particular technical measures.

Storage conditions : Keep container closed when not in use.

Incompatible products : Oxidizing agent. Strong acids. Strong bases.

Special rules on packaging : Keep only in original container.

7.3. Specific end use(s)

No additional information available

Safety Data Sheet

according to Regulation (EC) No. 453/2010

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Materials for protective clothing	: Not required for normal conditions of use
Hand protection	: In case of repeated or prolonged contact wear gloves
Eye protection	: Safety glasses
Skin and body protection	: Not required for normal conditions of use
Respiratory protection	: Not required for normal conditions of use



SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Mobile liquid.
Colour	: Yellow.
Odour	: lemon-like.
Odour threshold	: No data available
pH	: 3.5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 1.01
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No additional information available

10.4. Conditions to avoid

No additional information available

Safety Data Sheet

according to Regulation (EC) No. 453/2010

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

No additional information available

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Acute toxicity	: Not classified
Skin corrosion/irritation	: Not classified pH: 3.5
Serious eye damage/irritation	: Causes serious eye irritation. pH: 3.5
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information**12.1. Toxicity**

Cocamidopropyl betaine (147170-44-3)	
LC50 fishes 1	> 1 (1 - 10) mg/kg
EC50 Daphnia 1	> 1 (1 - 10) mg/l
ErC50 (other aquatic plants)	> 1 (1 - 10) mg/l
NOEC chronic fish	<= 1 mg/l
NOEC chronic crustacea	<= 1 mg/l
N,N-dimethyltetradecylamine N-oxide (3332-27-2)	
LC50 fishes 1	2.4 mg/l
EC50 other aquatic organisms 1	1.1 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 0.08 mg/l IC50 algae (72 h) mg/l

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

No additional information available

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

Not regulated for transport

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable

Proper Shipping Name (IMDG) : Not applicable

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Proper Shipping Name (IATA) : Not applicable

14.3. Transport hazard class(es)**ADR**

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable

Packing group (IMDG) : Not applicable

Packing group (IATA) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No

Marine pollutant : No

Other information : No supplementary information available

14.6. Special precautions for user**- Overland transport**

No data available

- Transport by sea

No data available

- Air transport

No data available

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****15.1.1. EU-Regulations**

Contains no substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

15.1.2. National regulations**Germany**

VwVwS Annex reference : Water hazard class (WGK) 1, slightly hazardous to water (Classification according to VwVwS, Annex 4)

12th Ordinance Implementing the Federal Immission Control Act - 12.BImSchV : Is not subject of the 12. BImSchV (Hazardous Incident Ordinance)

15.2. Chemical safety assessment

No additional information available

SECTION 16: Other information

Full text of R-, H- and EUH-phrases:

Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2

Safety Data Sheet

according to Regulation (EC) No. 453/2010

H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation
H412	Harmful to aquatic life with long lasting effects

SDS EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product