

# SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

## 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/ UNDERTAKING

### 1.1 **Product identifier:**

Product name : NCF correction fluid  
Product code : Not available

### 1.2 **Relevant identified uses of the mixture and uses advises against:**

#### 1.2.1 **Relevant identified uses**

Use of the substance/ mixture : Correction fluid

#### 1.2.2 **Uses advised against**

: No additional information available

### 1.3 **Details of the supplier of the safety data sheet**

Manufacturer / Supplier: Snopake Limited  
28 Perivale Park  
Horsenden Lane South,  
Perivale  
UB6 7RJ  
+44 208 991 1666  
[uksales@snopake.com](mailto:uksales@snopake.com)

1.4 **Emergency Telephone No** : +44 208 991 1666

## 2. HAZARDS IDENTIFICATION:

### 2.1 **Classification of substance or mixture**

Classification according to Regulation (EC) No 1272/2008

Flammable liquids: Category 2

Aquatic Chronic: Category 2

Skin irritation: Category 2

Specific target organ toxicant-single exposure: Category 3

H225 : Highly flammable liquid and vapour

H411 : Toxic to aquatic life with long lasting effects.

H315 : Causes skin irritation

H336 : May cause drowsiness or dizziness

### 2.2 **Label elements**

Labelling according to Regulation (EC) No 1272/2008

Hazard Pictograms:



Signal word

: Danger

Hazard statements

: H225

Highly flammable liquid and vapour

: H315

Causes skin irritation

: H336

May cause drowsiness or dizziness

: H411

Toxic to aquatic life with long lasting effects

Precautionary statements: P102

: Keep out of the reach of children

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

# SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

P210 : Keep away from heat/sparks/open flames/hot surfaces.  
— No smoking.

P303+P361+P353 : IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

Hazard ingredients

: Hydrocarbon, C6-C7, isoalkanes, cyclics, <5% n-hexane.

**2.3 Other hazards** : No additional information available

## 3. COMPOSITION / INFORMATION ON INGREDIENTS

**3.1 Substances** : Not applicable

**3.2 Mixtures**

Component	EC No	%	Classification according to Regulation (EC) No. 1272/ 2008[CLP]
Hydrocarbons, C6-C7, isoalkanes, cyclics, <5% n-hexane	926-605-8	25-50	Flammable liq.2, H225; Asp.Tox.1, H304; Aquatic chronic, H411; Skin irrit 2, H315; STOT SE3, H336;
Titanium dioxide	236-675-5	35-45	Not classified

Other information: This substance is categorized as Hydrocarbons, C6-7, isoalkanes, cyclics, <5% n-hexane, under HCSC, EC No 926-605-8  
Original substance name (EINECS): Naphtha (petroleum), hydro treated light.  
CAS-No is 64742-49-0

## 4. FIRST AID MEASURES

**4.1 Description of first aid measures**

First-aid measures after inhalation : Remove victim from exposure to fresh air. Remove contaminated clothing and loosen remaining clothing. Allow patient to assume most comfortable position and keep warm. Keep at rest until fully recovered. Seek medical advice if effects persist.

First-aid measures after ingestion : Rinse mouth with water. Seek immediate assistance.

First-aid measures after eye contact : Irrigate with copious quantities of water for 15 minutes. In all cases of eye contamination, it is a sensible precaution to seek medical advice.

First-aid measures after skin contact : Wash contaminated skin with plenty of soap and water. Remove contaminated clothing and wash before re-use. If irritation occurs seek medical advice.

**4.2 Most important symptoms and effects, both acute and delayed:**

No further information available.

**4.3 Indication of any immediate medical attention and special treatment :**

No further information available.

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

## SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

### 5. FIRE FIGHTING MEASURES & EMERGENCY ACTIONS

#### 5.1 *Extinguishing Media*

Suitable extinguisher agents: : Foam, carbon dioxide, dry chemical powder.  
Unsuitable extinguisher media : Full Water Jet

#### 5.2 *Special hazards arising from the substance/ mixture:*

Can form explosive gas-air mixture. Formation of toxic gases during heating or in case of fire.

#### 5.3 *Advice for fire-fighter*

: Fire fighters to wear self-contained breathing apparatus if risk of exposure to vapour or products of combustion.

### 6. ACCIDENTAL RELEASE MEASURES

#### 6.1 *Personal precautions, protective equipment and emergency procedures:*

Avoid contact with spilled material. Warn or evacuate occupants in surrounding and downwind areas if required, due to toxicity or flammability of the material. See Section 5 for fire fighting information. See Section 8 for advice on the minimum requirements for personal protective equipment.

#### 6.2 *Environmental precautions*

: Do not allow to enter drains or water courses.

#### 6.3 *Methods and material for containment and cleaning up:*

For containment : Absorb with inert material (vermiculite, diatomaceous earth or universal binder)  
Methods for cleaning up : Dispose the materials in accordance to local authority.

#### 6.4 *Reference to other sections*

: See Section 7 for safe handling, Section 13 on information of waste disposal.

### 7. HANDLING AND STORAGE

#### 7.1 *Precaution for safe handling*

Precaution for safe handling : Store away from oxidizing agents, sources of heat or ignition open flames or spark. Avoid contact with skin and eyes  
Hygiene measures : Wash hand after handling product

#### 7.2 *Condition for safe storage*

: Keep container tightly closed. Store in cool and well-ventilated area. Keep away from foodstuff.

#### 7.3 *Specific end use:*

: No further information available.

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

# SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

### 8.1 Control parameters

Titanium dioxide(CAS No. 13463-67-7)	WEL Long-term	10 mg/m <sup>3</sup> (Total inhalable)
	WEL Long-term	4 mg/m <sup>3</sup> (Respirable)

### 8.2 Exposure control

Hand protection	: Wear protective gloves when required. Nitrile gloves are recommended.
Eye protection	: Safety goggles
Skin and body protection	: Chemical resistant gloves and chemical resistance clothing
Respiratory protection	: Approved respirator. Type A filter respirators are recommended.
Environmental exposure controls	: Prevent product in entering water, drains and soil.
Other information	: Do not heat the product.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

Physical State	
Colour	
Odour	
Odour threshold	
pH	: No data available
Melting point/ range	: No data available
Boiling point/ range	: No data available
Flash point	: 8.5 degree Celsius
Auto ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Product is not self igniting
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility with water	: Insoluble
Log Pow	: No data available
Viscosity, Kinematic	: 25-30 mm <sup>2</sup> /s (kinematics at 40 degC)
Viscosity, Dynamic	: No data available
Explosives properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

**9.2 Other information** : No further information available.

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

# SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

## 10. STABILITY AND REACTIVITY

- 10.1 Reactivity** : No hazard to be specially known
- 10.2 Chemical stability** : Stable under recommended storage and handling condition (Section 7)
- 10.3 Possibility of hazard reactions** : No dangerous reactions known.
- 10.4 Conditions to be avoided** : Avoid heat, sparks, open flames and other ignition sources.
- 10.5 Incompatible materials** : Strong oxidizers.
- 10.6 Hazardous decomposition products** : Product does not decompose under ambient temperatures.

## 11. TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

- Acute toxicity : No further information available  
*Hydrocarbons, C6-C7, isoalkanes, cyclics, <5% n-hexane (926-605-8)*  
Oral LD 50 > 5000 mg/kg, OECD Guideline 401  
Dermal LD 50 > 3350 mg/kg, OECD Guideline 402  
Inhalative LC 50/4h > 20 mg/l (Vapour), OECD Guideline 403  
*Titanium dioxide (13463-67-7)*  
Oral LD 50 > 5000 mg/kg, OECD Guideline 425  
Dermal LD 50 > 5000 mg/kg
- Skin corrosion/ irritation : Moderately irritating to skin with prolonged exposure  
Serious eye damage/ irritation : No further information available  
Respiratory/ skin sensitization : No sensitizing effect known  
Germ cell mutagenicity : No further information available  
Carcinogenicity : No further information available  
Reproductive toxicity : No further information available  
Specific target organ toxicity (single exposure) : May cause drowsiness or dizziness  
Specific target organ toxicity (repeated exposure) : No further information available  
Aspiration hazard : No further information available  
(kinematic viscosity is > 20.5mm<sup>2</sup>/s)

## 12. ECOLOGICAL INFORMATION

### 12.1 Toxicity

- Ecology- general : Toxic to aquatic organisms, with long-lasting effect.  
*Hydrocarbons, C6-C7, isoalkanes, cyclics, <5% n-hexane (926-605-8)*  
Algentoxizitat: >1 - < 10mg/l (Algae) (LC50)  
Bakterientoxizitat: >1 - < 10mg/l (bacteria) (LC50)  
Fischtoxizitat: >1 - < 10mg/l (fish) (LC50)

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

## SAFETY DATA SHEET according to Regulations (EC) No. 1907/2006 (REACH)

Product : **CORRECTION FLUID**

Revision date: Jan 2018

- 12.2** *Persistent and degradability* : No further information available
- 12.3** *Bioaccumulation potential* : No further information available
- 12.4** *Mobility in soil* : No further information available
- 12.5** *Results of PBT and vPvB assessment* : No further information available
- 12.6** *Other adverse effects* : No further information available

### 13. DISPOSAL CONSIDERATION

#### 13.1 *Waste treatment methods*

Waste disposal recommendation      Avoid discharging waste into rivers and drains. Collect and segregate waste in appropriate labelled containers.  
Disposal is in accordance to relevant local regulations.

### 14. TRANSPORT INFORMATION

- 14.1** *UN number*  
UN - No (IMDG/ ADR/ IATA) : 1263
- 14.2** *UN proper shipping name*  
UN proper shipping name (IMDG/ ADR/ IATA) : PAINT RELATED MATERIAL
- 14.3** *Transport hazard class(es)*  
Class : 3
- 14.4** *Packing group*  
Packing group (UN/ IMDG) : II
- 14.5** *Environmental hazards* : Product contains environmentally hazardous substances: Naphtha (petroleum), hydrotreated light
- 14.6** *Special precautions for user* : No further information available
- 14.7** *Transport in bulk according to Annex II of Marpol and the IBC Code* : Not applicable

This information is given in good faith and is based on extensive experience and actual state of art. It does not represent a guarantee for the properties of the product.

### 15. REGULATORY INFORMATION

