


THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



**SPECIFICHE DI CARICO:**

- Componente spessore 4,0 mm forza F=20N min
- Componente spessore 4,5 mm forza F=25N min
- Componente spessore 5,0 mm forza F=30N min

**CHARGE SPECIFICATIONS:**

- Thickness Component 4,0 mm force F=20N min
- Thickness Component 4,5 mm force F=25N min
- Thickness Component 5,0 mm force F=30N min



**AAVID THERMALLOY**  
EUROPE [www.aavidthermalloy.com](http://www.aavidthermalloy.com)

Via XXV Aprile, 82  
40067 Castiglione - Bologna ITALY  
Tel. +39 051 764011  
Fax. +39 051 764028

Cheney Manor  
SWINDON WILTS SN1 1BN UK  
Tel. +44 1793 401400  
Fax +44 1793 810888

COMPANY WITH QUALITY SYSTEM CERTIFIED BY DNV ISO 9001

COMPANY WITH QUALITY SYSTEM CERTIFIED BY BSI ISO 9002

Die n.	MATERIAL EN10132-4 C67S 0.35 x 4
Factor	GENERAL TOLERANCES
Part n.	
Area mm <sup>2</sup>	FINISH See note
Weight	
Notes:	Zincatura bianca alta resistenza \ Zn high resistance plated Tratt termico/thermal treatment: BONIFICA 42-46 HRC all dimensions in mm
Drawn	S.Melotto
Check	

REV	Date	Revision description
B	19Oct11	Confirm drawing
A	25Sep07	ORIGINAL (was ZA3899)

DRAWING n.		439647	
Vls. n.			
Description: 5901G Spring clip			
Format	Scale	1	
By	A4	1:1	