

NSYSM14840

Spacial SM compact enclosure without mounting plate - 1400x800x400 mm



Main

| | |
|-----------------------------|--|
| Range | Spacial |
| Product name | Spacial SM |
| Product or component type | Compact enclosure |
| Device application | Multi-purpose |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 1 cable gland plate 1 door 1 locking system with handle for door 4 mounting plate bracket |
| Removable parts | Door fixed by screws for hinge Mounting plate bracket fixed by screws |
| Enclosure nominal height | 1400 mm |
| Enclosure nominal width | 800 mm |
| Enclosure nominal depth | 400 mm |

Complementary

| | |
|-----------------------------|--|
| Number of doors | 1 on front |
| Door opening side | Reversible 120 ° |
| Door type | Plain |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Body type | Single piece body with welded rear panel Front part forming a rigid frame with welded corners |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Standard |
| Cable entry | 1 entry |
| Material | Sheet steel for body Sheet steel for door Zamak for hinge |
| Surface finish | Epoxy-polyester powder |
| Colour | Enclosure : grey RAL 7035 Handle : black RAL 9005 |
| Accessibility for operation | Front |

Environment

| | |
|-------------------------|------------------------------|
| standards | IEC 62208 |
| product certifications | BV DNV UL |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
