

NSYCVF38M230PF

ClimaSys forced vent. IP54, 38m³/h, 230V, with outlet grille and filter G2



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter: 38 m ³ /h at 50 Hz Free flow rate with standard filter: 39 m ³ /h at 60 Hz
[Us] rated supply voltage	150...250 V
Input voltage	230 V 50/60 Hz

Complementary

Power range	4.5 W 50 Hz 4.8 W 60 Hz
[In] rated current	0.16 A 50 Hz 0.17 A 60 Hz
Noise level	40...41 dB
Bearing type	Ball
Height	External: 137 mm
Width	External: 117 mm
Depth	External: 49 mm
Cut-out dimensions	92 x 92 mm
Product weight	0.22 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	29 Pa flow rate 0 m ³ /h
Connections - terminals	Cable
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software
Installed device	- MUST NOT be connected to a power conversion module, an inverter or UPS type of power supply

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------