


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		H2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

D



- 1

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2

WIRE RANGE: 0.12-0.4mm² (26-22 AWG).
- 3



INSULATION RANGE: 1.20-1.75 [.047-.069] DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5


0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C



B



6	OBSOLETE	5	0.20 [.008] PH BRZ	4-770986-1
		5	0.20 [.008] BRASS	1-770986-0
		1	0.20 [.008] BRASS	770986-3
	PRE-TIN		0.20 [.008] BRASS	770986-1
	FINISH		MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 18OCT02	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. JONES 18OCT02				
		APVD C. JONES 18OCT02	NAME SOCKET, LOOSE PIECE, MINI UNIVERSAL MATE-N-LOK(TM)			
		PRODUCT SPEC				
MATERIAL SEE TABLE		APPLICATION SPEC				
		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=770986	RESTRICTED TO -
FINISH SEE TABLE		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV H2	

