


Uninsulated Crimp Ring Terminal, 1440pcs 0.5 - 6.0mm² Wire size, M3 - M8 Stud size



Technical Data:

Material: Copper
Plating: Tin
Max. voltage rating: 600V
Max. temperature rating: 300°C

Wire Guide	Cross Section	Dimension (mm)								Stud size	Quantity
		L	L1	L2	øD	øD1	T	R	øR1		
20-17 AWG	0.5-1.0 mm ²	12.5 ±1.0	5.0 ±0.2	4.8 ±0.2	3.4 ±0.3	1.7 ±0.2	0.7 ±0.05	5.7 ±0.2	3.15 ±0.2	M3	200 Pcs
		12.6 ±1.0	5.5 ±0.2	4.8 ±0.2	3.4 ±0.3	1.7 ±0.2	0.7 ±0.05	5.7 ±0.2	3.6 ±0.2	M3.5	200 Pcs
		14.5 ±1.0	6.8 ±0.2	4.8 ±0.2	3.4 ±0.3	1.7 ±0.2	0.7 ±0.05	6.6 ±0.2	4.3 ±0.2	M4	200 Pcs
		15.7 ±1.0	7.2 ±0.2	4.8 ±0.2	3.4 ±0.3	1.7 ±0.2	0.7 ±0.05	8.0 ±0.2	5.3 ±0.2	M5	150 Pcs
16-14 AWG	1.5-2.5 mm ²	12.4 ±1.0	4.3 ±0.2	4.9 ±0.2	4.1 ±0.3	2.4 ±0.2	0.8 ±0.05	6.6 ±0.2	3.15 ±0.2	M3	150 Pcs
		14.8 ±1.0	6.5 ±0.2	4.9 ±0.2	4.1 ±0.3	2.4 ±0.2	0.8 ±0.05	6.6 ±0.2	4.3 ±0.2	M4	150 Pcs
		16.8 ±1.0	7.5 ±0.2	4.9 ±0.2	4.1 ±0.3	2.4 ±0.2	0.8 ±0.05	8.5 ±0.2	5.3 ±0.2	M5	75 Pcs
		16.8 ±1.0	7.5 ±0.2	4.9 ±0.2	4.1 ±0.3	2.4 ±0.2	0.8 ±0.05	9.6 ±0.2	6.3 ±0.2	M6	75 Pcs
		21.8 ±1.0	11.4 ±0.2	4.9 ±0.2	4.1 ±0.3	2.4 ±0.2	0.8 ±0.05	12.1 ±0.2	8.3 ±0.2	M8	40 Pcs
12-10 AWG	4.0-6.0 mm ²	15.8 ±1.0	5.6 ±0.2	7.0 ±0.2	5.5 ±0.3	3.4 ±0.2	1.0 ±0.05	7.2 ±0.2	4.2 ±0.2	M4	75 Pcs
		20.0 ±1.0	8.5 ±0.2	7.0 ±0.2	5.5 ±0.3	3.4 ±0.2	1.0 ±0.05	9.5 ±0.2	5.3 ±0.2	M5	75 Pcs
		23.5 ±1.0	10.5 ±0.2	7.0 ±0.2	5.5 ±0.3	3.4 ±0.2	1.0 ±0.05	12.1 ±0.2	6.5 ±0.2	M6	50 Pcs