



## MKB-0325



Die profile



Crimp profile

MKB-0325 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on uninsulated copper tube connectors on wires ranging from 0,35-2,5 mm<sup>2</sup>.

### Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

### Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information See instruction sheet.

- Compact, pocketable design.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

### Technical data

Lenght :	212 mm/8,35"
Height :	72 mm/2,83"
Weight :	470 gr/1,04 lbs
Connector:	Uninsulated / Copper tube
Description:	Indent crimp
Wire size awg:	22-14 AWG
Wire size mm <sup>2</sup> :	0,35-2,5 mm <sup>2</sup> / 22-14 AWG

Distributors address info

--