

5mm Round Super Blue LED Lamps


Black prominent bezel

Order code: **42-1004**

MPN: 5BPINDB



Package Dimensions (mm):



Notes:

1. All dimensions in millimetres
2. An epoxy meniscus may extend about 1.5mm (0.059in) down to the lead
3. Tolerances unless stated ± 0.25 mm

Features:

- Reliable and robust

Descriptions:

- The series is specially designed for applications requiring higher brightness

Applications:

- TV Set
- Monitor
- Telephone



5mm Round Super Blue LED Lamps

Black prominent bezel

Order code: 42-1004

Chip		Lens Colour
Material	Emitted Colour	
InGaN	Super Blue	Blue Diffused

■ Absolute maximum rating at Ta=25°C

Parameter	Symbol	Rating	Unit
Continuous Forward Current	I_F	30	mA
Operating Temperature	T_{opr}	-40~+85	°C
Storage Temperature	T_{stg}	-40~+100	°C
Soldering Temperature	T_{sol}	260±5	°C
Electrostatic Discharge	ESD	1000	V
Power Dissipation	P_D	120	mW
Peak Forward Current (Duty 1/10@1KHz)	I_F (Peak)	100	mA
Reverse Voltage	V_R	5	V

■ Electrical – Optical characteristics:

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	I_v	2600	4000	/	mcd	$I_F=20mA$
Viewing Angle	2θ 1/2	/	50	/	deg	- - -
Peak Wavelength	λ_p	/	472	/	nm	$I_F=20mA$
Dominant Wavelength	λ_d	/	470	/	nm	$I_F=20mA$
Spectrum Radiation Bandwidth	$\Delta \lambda$	/	30	/	nm	$I_F=20mA$
Forward Voltage	V_F	/	3.5	4.0	V	$I_F=20mA$
Reverse Current	I_R	/	/	10	µA	$V_R=5V$

■ Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.


Confidence level: 90%

LTPD: 10%


NO	ITEM	Test Conditions	Test hours/cycle	Sample Q'ty	Ac/Re
1	Solder Heat	Temp: 260°C±5°C	5 sec	22 pcs	0/1
2	Temperature Cycle	H: +100°C 15min ↓ 5min L: -40°C 15min	50 cycles	22 pcs	0/1
3	Thermal Shock	H: +100°C 15min ↓ 10sec L: -10°C 15min	50 cycles	22 pcs	0/1
4	High Temperature Storage	Temp: 100°C	1000 hrs	22 pcs	0/1
5	Low Temperature Storage	Temp: -40°C	1000 hrs	22 pcs	0/1
6	DC Operating Life	$I_F=20mA$	1000 hrs	22 pcs	0/1
7	High Temperature/High Humidity	85°C/85%RH	1000 hrs	22 pcs	0/1

Typical electro-optical characteristics curves:


The data typical and the value are not guaranteed




RADIATION DIAGRAM




RELATIVE LUMINOUS INTENSITY Vs. WAVELENGTH




LUMINOUS INTENSITY Vs. AMBIENT TEMPERATURE



MAX FORWARD CURRENT Vs. AMBIENT TEMPERATURE



FORWARD CURRENT Vs. FORWARD VOLTAGE



LUMINOUS INTENSITY Vs. FORWARD CURRENT