

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
 Name : ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER
 UFI : HHA8-U0WF-S00H-4ERY
 Product code : 33-428
 Type of product : Detergent
 Product group : Trade product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
 Industrial/Professional use spec : For professional use only
 Use of the substance/mixture : Washing and cleaning products (including solvent based products)

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

ARROW COUNTY SUPPLIES LIMITED,
 Arrow House,
 Longden Road,
 Shrewsbury,
 Shropshire,
 SY3 9AE.

Tel: 0044 (0) 1743 283 600 Fax: 0044 (0) 1743 283 601

Email: sales@arrowcounty.com Web: www.arrowcounty.com

1.4. Emergency telephone number

Emergency number : 0044 (0) 1743 283600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315
 Serious eye damage/eye irritation, Category 2 H319
 Skin sensitisation, Category 1 H317
 Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

May cause an allergic skin reaction. Causes serious eye irritation. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

Signal word (CLP)	: Warning
Hazardous ingredients	: (R)-p-mentha-1,8-diene; d-limonene
Hazard statements (CLP)	: H315 - Causes skin irritation. H317 - May cause an allergic skin reaction. H319 - Causes serious eye irritation. H412 - Harmful to aquatic life with long lasting effects.
Precautionary statements (CLP)	: P261 - Avoid breathing fume, mist, vapours. P264 - Wash hands, forearms and face thoroughly after handling. P273 - Avoid release to the environment. P280 - Wear protective clothing, protective gloves, eye protection. P302+P352 - IF ON SKIN: Wash with plenty of water. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P332+P313 - If skin irritation occurs: Get medical advice/attention. P337+P313 - If eye irritation persists: Get medical advice/attention. P362+P364 - Take off contaminated clothing and wash it before reuse. P501 - Dispose of contents and container to an approved waste disposal plant.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
(2-methoxymethylethoxy)propanol [DPGME] substance with a Community workplace exposure limit	(CAS-No.) 34590-94-8 (EC-No.) 252-104-2	3 – 5	Not classified
(R)-p-mentha-1,8-diene; d-limonene	(CAS-No.) 5989-27-5 (EC-No.) 227-813-5 (EC Index-No.) 601-029-00-7	1 – 3	Flam. Liq. 3, H226 Skin Irrit. 2, H315 Skin Sens. 1, H317 Aquatic Acute 1, H400 Aquatic Chronic 1, H410
METHOXYMETHYLBUTANOL	(CAS-No.) 56539-66-3 (EC-No.) 260-252-4	1 – 3	Eye Irrit. 2, H319
Benzenesulfonic Acid, 4-C10-13-SEC-ALKYL DERIVS., COMPDS. WITH TRIETHANOLAMINE	(EC-No.) 939-464-2	0.1 – 3	Skin Irrit. 2, H315 Eye Dam. 1, H318 Aquatic Chronic 3, H412

Specific concentration limits:

Name	Product identifier	Specific concentration limits
Benzenesulfonic Acid, 4-C10-13-SEC-ALKYL DERIVS., COMPDS. WITH TRIETHANOLAMINE	(EC-No.) 939-464-2	(1 ≤C < 60) Skin Irrit. 2, H315 (60 ≤C < 100) Skin Corr. 1C, H314

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water. Take off contaminated clothing. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell. Rinse mouth out with water. Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Immediately call a POISON CENTER/doctor.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: May cause an allergic skin reaction.
Symptoms/effects after eye contact	: Eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : The product is not flammable. Water spray. Use extinguishing agent suitable for surrounding fire. Dry powder. Foam. Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.

Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray. Wear personal protective equipment.

Hygiene measures : Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

(2-methoxymethylethoxy)propanol [DPGME] (34590-94-8)		
EU	Local name	(2-Methoxymethylethoxy)-propanol
EU	IOELV TWA (mg/m ³)	308 mg/m ³
EU	IOELV TWA (ppm)	50 ppm
EU	Notes	Skin
United Kingdom	Local name	(2-methoxymethylethoxy) propanol
United Kingdom	WEL TWA (mg/m ³)	308 mg/m ³
United Kingdom	WEL TWA (ppm)	50 ppm
United Kingdom	Remark (WEL)	Sk (Can be absorbed through the skin. The assigned substances are those for which there are concerns that dermal absorption will lead to systemic toxicity)

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Hand protection:

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

Protective gloves

Eye protection:

Safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: dark orange.
Odour	: Fruity.
Odour threshold	: No data available
pH	: 8 – 9
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: < 0 °C Not applicable
Freezing point	: < 0
Boiling point	: > 100 °C
Flash point	: > 55 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: ≈ 1.005
Solubility	: Soluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Product is not explosive.
Oxidising properties	: Oxidising solids Not applicable.
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	: Not classified
Skin corrosion/irritation	: Causes skin irritation. pH: 8 – 9
Serious eye damage/irritation	: Causes serious eye irritation. pH: 8 – 9
Respiratory or skin sensitisation	: May cause an allergic skin reaction.
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Harmful to aquatic life with long lasting effects.

12.2. Persistence and degradability

CITRA CLEAN CONCENTRATE	
Persistence and degradability	The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

UN-No. (ADR)	: Not applicable
UN-No. (IMDG)	: Not applicable
UN-No. (IATA)	: Not applicable
UN-No. (ADN)	: Not applicable
UN-No. (RID)	: Not applicable

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

Proper Shipping Name (IMDG)	: Not applicable
Proper Shipping Name (IATA)	: Not applicable
Proper Shipping Name (ADN)	: Not applicable
Proper Shipping Name (RID)	: Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

ADN

Transport hazard class(es) (ADN) : Not applicable

RID

Transport hazard class(es) (RID) : Not applicable

14.4. Packing group

Packing group (ADR)	: Not applicable
Packing group (IMDG)	: Not applicable
Packing group (IATA)	: Not applicable
Packing group (ADN)	: Not applicable
Packing group (RID)	: Not applicable

14.5. Environmental hazards

Dangerous for the environment	: No
Marine pollutant	: No
Other information	: No supplementary information available

14.6. Special precautions for user

- Overland transport

Not applicable

- Transport by sea

Not applicable

- Air transport

Not applicable

- Inland waterway transport

Not applicable

- Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Allergenic fragrances > 0,01%:

d-Limonene

Detergent Regulation (648/2004/EC): Labelling of contents:

ANDARTA ELIMINATOR MULTI PURPOSE CLEANER & DEGREASER

Safety Data Sheet

according to Regulation (EU) 2015/830

Component	%
non-ionic surfactants	5-<15%
anionic surfactants	<5%
perfumes	
D-LIMONENE	

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

Revision - See : *.

Abbreviations and acronyms:

ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
EC50	Median effective concentration
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
PBT	Persistent Bioaccumulative Toxic
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
vPvB	Very Persistent and Very Bioaccumulative

Full text of H- and EUH-statements:

Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Skin Corr. 1C	Skin corrosion/irritation, Category 1, Sub-Category 1C
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
H226	Flammable liquid and vapour.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

SDS EU (Reach Annex II) GREEN

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.