

MAGIX - SOLVENT WHITEBOARD CLEANER

Page: 1

Compilation date: 12/12/2011

Revision date: 08/12/2014

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: MAGIX - SOLVENT WHITEBOARD CLEANER

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Eastpoint

Rotterdam Rd Lowestoft

NR32 2EX

Tel: +44(0)1502 525555

Email: info@eastpointglobal.com

1.4. Emergency telephone number

Emergency tel: +44(0)1502 525555

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H336; Eye Irrit. 2: H319; Flam. Liq. 2: H225

Most important adverse effects: Highly flammable. Irritating to eyes. Vapours may cause drowsiness and dizziness.

2.2. Label elements

Label elements under CLP:

Hazard statements: H225: Highly flammable liquid and vapour. H319: Causes serious eye irritation. H336: May cause drowsiness or dizziness. Signal words: Danger Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



Precautionary statements: P280: Wear protective gloves/protective clothing/eye protection/face protection. P303+361+353: IF ON SKIN (or hair): Remove immediately all contaminated clothing. Rinse skin with water.

MAGIX - SOLVENT WHITEBOARD CLEANER

P304+340: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312: Call a POISON CENTER or doctor if you feel unwell.
P370+378: In case of fire: Use CO2 OR POWDER for extinction.

Label elements under CHIP:

Hazard symbols: Highly flammable.

Irritant.



Risk phrases: R11: Highly flammable.

R36: Irritating to eyes.

R67: Vapours may cause drowsiness and dizziness.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ETHANOL

EINECS	CAS	CHIP Classification	CLP Classification	Percent
200-578-6	64-17-5	F: R11 Substance with a Community workplace exposure limit.	Flam. Liq. 2: H225	70-90%

PROPAN-2-OL

	200-661-7	67-63-0	F: R11; Xi: R36; -: R67	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	10-30%
--	-----------	---------	-------------------------	--	--------

METHANOL

200-659-6	67-56-1	F: R11; T: R23/24/25; T:	Flam. Liq. 2: H225; Acute Tox. 3: H331;	1-10%
		R39/23/24/25	Acute Tox. 3: H311; Acute Tox. 3: H301;	
			STOT SE 1: H370	

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash

immediately with plenty of soap and water.

Page: 2

MAGIX - SOLVENT WHITEBOARD CLEANER

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

MAGIX - SOLVENT WHITEBOARD CLEANER

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ETHANOL

Workplace exposure limits:

•	•		•	
State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1920 mg/m3	-	-	-

Respirable dust

PROPAN-2-OL

UK	999 mg/m3 (400ppm)	1250 mg/m3 (500ppm)	-	-
METHANOL				
UK	266 mg/m3 (200ppm)	333 mg/m3 (250ppm)	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls					
Engineering measures:	Ensure there is sufficient ventilation of the area. Ensure lighting and electrical				
	equipment are not a source of ignition.				
Respiratory protection:	Self-contained breathing apparatus must be available in case of emergency.				
Hand protection:	Protective gloves.				
Eye protection:	Safety glasses. Ensure eye bath is to hand.				
Skin protection:	Protective clothing.				

MAGIX - SOLVENT WHITEBOARD CLEANER

Page: 5

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties	

State: Liquid Colour: Colourless

Odour: Alcoholic

Solubility in water: Soluble

Viscosity: Non-viscous

Boiling point/range°C: >35

Relative density: 0.79

Flash point°C: <21

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ETHANOL

IVN	RAT	LD50	1440	mg/kg
ORL	MUS	LD50	3450	mg/kg

MAGIX - SOLVENT WHITEBOARD CLEANER

				Page
ORL	RAT	LD50	7060	mg/kg
PROPAN-2-OL				
IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg
METHANOL			1	
IVN	RAT	LD50	2131	mg/kg
ORL	MUS	LD50	7300	mg/kg
ORL	RAT	LD50	5628	mg/kg

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

METHANOL

ALGAE	72H IC50	8000	mg/l
DAPHNIA	48H EC50	24500	mg/l
FISH	96H LC50	10800	mg/l

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

MAGIX - SOLVENT WHITEBOARD CLEANER

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Marine pollutant: No

Section 14: Transport information

14.1. UN number

UN number: UN1993

14.2. UN proper shipping name

Shipping name: FLAMMABLE LIQUID, N.O.S.

(ETHANOL; PROPAN-2-OL)

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: ||

14.5. Environmental hazards

Environmentally hazardous: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 2

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

MAGIX - SOLVENT WHITEBOARD CLEANER

Section 16: Other information

Other information	
Other information:	This safety data sheet is prepared in accordance with Commission Regulation (EU) No
	453/2010.
	* indicates text in the SDS which has changed since the last revision.
Phrases used in s.2 and s.3:	H225: Highly flammable liquid and vapour.
	H301: Toxic if swallowed.
	H311: Toxic in contact with skin.
	H319: Causes serious eye irritation.
	H331: Toxic if inhaled.
	H336: May cause drowsiness or dizziness.
	H370: Causes damage to organs <or affected,="" all="" if="" known="" organs="" state=""> <state of<="" route="" td=""></state></or>
	exposure if it is conclusively proven that no other routes of exposure cause the hazard>.
	R11: Highly flammable.
	R23/24/25: Toxic by inhalation, in contact with skin and if swallowed.
	R36: Irritating to eyes.
	R39/23/24/25: Toxic: danger of very serious irreversible effects through inhalation, in
	contact with skin and if swallowed.
	R67: Vapours may cause drowsiness and dizziness.
Legend to abbreviations:	PNEC = predicted no effect level
	DNEL = derived no effect level
	LD50 = median lethal dose
	LC50 = median lethal concentration
	EC50 = median effective concentration
	IC50 = median inhibitory concentration
	dw = dry weight
	bw = body weight
	cc = closed cup
	oc = open cup
	MUS = mouse
	GPG = guinea pig
	RBT = rabbit
	HAM = hamster
	HMN = human
	MAM = mammal
	PGN = pigeon
	IVN = intravenous
	SCU = subcutaneous
	SKN = skin

MAGIX - SOLVENT WHITEBOARD CLEANER

Page: 9

 DRM = dermal

 OCC = ocular/corneal

 PCP = phycico-chemical properties

 Legal disclaimer:

 The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.