

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name

edding 366 whiteboard marker (black)

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Ink for use in drawliners

Uses advised against

No data available.

1.3 Details of the supplier of the safety data sheet

Address

edding International GmbH

Bookkoppel 7

D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

Information provided by / telephone

+49 (0)4102 - 808-0

Advice on Safety Data Sheet

sdb_info@umco.de

1.4 Emergency telephone number

For medical advice (in German and English):

+49 (0)30 30686 790 (Giftnotruf Berlin)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification in accordance with Regulation (EC) No 1272/2008 (CLP)

Eye Irrit. 2; H319

Flam. Liq. 2; H225

STOT SE 3; H336

Classification information

This product is assessed and classified using the methods and criteria below referred to in Article 9 of Regulation (EC) n° 1272/2008:

Physical hazards: determined through assessment data based on the methods or standards referred to in part 2 of Annex I to CLP

Health hazards and environmental hazards: determined through toxicological and ecotoxicological assessment data based on the methods or standards referred to in Part 3, 4 and 5 of Annex I to CLP.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 (CLP Regulation)

Hazard pictograms



GHS02



GHS07

Signal word

Danger

Hazardous component(s) to be indicated on label:

propan-2-ol

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Hazard statements

H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P271 Use only outdoors or in a well-ventilated area.
P370+P378 In case of fire: Use water spray, extinguishing powder, foam or CO2 to extinguish.
P405 Store locked up.
P501 Dispose of contents/container in accordance with local and national regulations.

2.3 Other hazards

No data available.

SECTION 3: Composition/information on ingredients
3.1 Substances

Not applicable. The product is not a substance.

3.2 Mixtures
Chemical characterization

Mixture (preparation)

Hazardous ingredients

No	Substance name		Additional information	
	CAS / EC / Index / REACH no	Classification (EC) 1272/2008 (CLP)	Concentration	%
1	ethanol			
	64-17-5 200-578-6 603-002-00-5 -	Flam. Liq. 2; H225	>= 50.00 - < 70.00	%-b.w.
2	propan-2-ol			
	67-63-0 200-661-7 603-117-00-0 -	Eye Irrit. 2; H319 Flam. Liq. 2; H225 STOT SE 3; H336	>= 25.00 - < 50.00	%-b.w.
3	CARBON BLACK			
	1333-86-4 215-609-9 - -	-	< 5.00	%-b.w.

Full Text for all H-phrases and EUH-phrases: pls. see section 16

3.3 Other information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

SECTION 4: First aid measures
4.1 Description of first aid measures
General information

In case of persisting adverse effects, consult a physician. Remove contaminated clothing and shoes immediately, and launder thoroughly before reusing.

After inhalation

Remove affected person from the immediate area. Ensure supply of fresh air.

After skin contact

Wash off immediately with soap and water.

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

After eye contact

Remove contact lenses. Rinse eye thoroughly under running water keeping eyelids wide open and protecting the unaffected eye (at least 10 to 15 minutes). Seek medical assistance.

After ingestion

Rinse mouth thoroughly with water. Call a doctor immediately. Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

No data available.

4.3 Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Foam; Carbon dioxide; Extinguishing powder

Unsuitable extinguishing media

No data available.

5.2 Special hazards arising from the substance or mixture

In the event of fire, the following can be released: Carbon dioxide (CO₂); Carbon monoxide (CO)

5.3 Advice for firefighters

Use self-contained breathing apparatus. Cool endangered containers with water spray jet. Wear protective clothing.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Keep away sources of ignition.

For emergency responders

No data available. Personal protective equipment (PPE) - see Section 8.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater. Do not discharge into the subsoil/soil.

6.3 Methods and material for containment and cleaning up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). When picked up, treat material as prescribed under heading "Disposal considerations".

6.4 Reference to other sections

No data available.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

Provide good ventilation of working area (local exhaust ventilation, if necessary). If workplace exposure limits are exceeded, respiratory protection approved for this particular job must be worn. Product inherent handling risks must be minimised taking the appropriate measures for protection and preventive actions. The working process should be designed to rule out the release of hazardous substances or skin contact as far as it is possible by the state of the art.

General protective and hygiene measures

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Do not inhale vapours. Clean skin thoroughly after work; apply skin cream.

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Advice on protection against fire and explosion

Vapours can form an explosive mixture with air. Take precautionary measures against static charges. Keep away from sources of heat and ignition. Use explosion-proof equipment/fittings and non-sparking tools.

7.2 Conditions for safe storage, including any incompatibilities

Technical measures and storage conditions

Keep container tightly closed and dry in a cool, well-ventilated place.

Requirements for storage rooms and vessels

Containers which are opened must be carefully closed and kept upright to prevent leakage. Always keep in containers of same material as the original one.

Advice on storage assembly

None known

7.3 Specific end use(s)

No data available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values

No	Substance name	CAS no.	EC no.
1	ethanol	64-17-5	200-578-6
List of approved workplace exposure limits (WELs) / EH40			
Ethanol			
	TWA	1920 mg/m ³	1000 ml/m ³
2	propan-2-ol	67-63-0	200-661-7
List of approved workplace exposure limits (WELs) / EH40			
Propan-2-ol			
	STEL	1250 mg/m ³	500 ml/m ³
	TWA	999 mg/m ³	400 ml/m ³
3	CARBON BLACK	1333-86-4	215-609-9
List of approved workplace exposure limits (WELs) / EH40			
Carbon black			
	STEL	7 mg/m ³	
	TWA	3.5 mg/m ³	

8.2 Exposure controls

Appropriate engineering controls

No data available.

Personal protective equipment

Respiratory protection

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

Eye / face protection

Safety glasses with side protection shield (EN 166)

Hand protection

Sufficient protection is given wearing suitable protective gloves checked according to i.e. EN 374, in the event of risk of skin contact with the product. Before use, the protective gloves should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Other

Normal chemical work clothing.

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Environmental exposure controls

No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Form/Colour		
liquid		
black		
Odour		
characteristic		
Odour threshold		
No data available		
pH value		
No data available		
Boiling point / boiling range		
Value	78.3	°C
Reference substance	CAS 64-17-5	
Melting point / melting range		
No data available		
Decomposition point / decomposition range		
No data available		
Flash point		
Value	13	°C
Reference substance	CAS 64-17-5	
Ignition temperature		
Value	390	°C
Auto-ignition temperature		
No data available		
Oxidising properties		
No data available		
Explosive properties		
No data available		
Flammability (solid, gas)		
No data available		
Lower flammability or explosive limits		
Value	2	% vol
Upper flammability or explosive limits		
Value	19.0	% vol
Vapour pressure		
No data available		
Vapour density		
No data available		
Evaporation rate		
No data available		
Relative density		
Value	0.823	

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Density	
No data available	
Solubility in water	
Remarks	insoluble
Solubility(ies)	
No data available	
Partition coefficient: n-octanol/water	
No data available	
Viscosity	
No data available	

9.2 Other information

Other information
No data available.

SECTION 10: Stability and reactivity**10.1 Reactivity**

No data available.

10.2 Chemical stability

No data available.

10.3 Possibility of hazardous reactions

No data available.

10.4 Conditions to avoid

Heat, naked flames and other ignition sources. air humidity

10.5 Incompatible materials

None known.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information**11.1 Information on toxicological effects**

Acute oral toxicity			
No	Substance name	CAS no.	EC no.
1	ethanol	64-17-5	200-578-6
LD50		6200	mg/kg bodyweight
Species	rat		
Source	Manufacturer		
2	propan-2-ol	67-63-0	200-661-7
LD50		5280	mg/kg bodyweight
Species	rat		
Source	Manufacturer		
Acute dermal toxicity			
No	Substance name	CAS no.	EC no.
1	propan-2-ol	67-63-0	200-661-7
LD50		12800	mg/kg bodyweight
Species	rabbit		
Source	Manufacturer		

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Acute inhalational toxicity			
No	Substance name	CAS no.	EC no.
1	propan-2-ol	67-63-0	200-661-7
LC50		72.6	mg/l
Duration of exposure		4	h
State of aggregation	Vapour		
Species	rat		
Source	Manufacturer		

Skin corrosion/irritation	
No data available	

Serious eye damage/irritation	
No data available	

Respiratory or skin sensitisation	
No data available	

Germ cell mutagenicity	
No data available	

Reproduction toxicity	
No data available	

Carcinogenicity	
No data available	

STOT-single exposure	
No data available	

STOT-repeated exposure	
No data available	

Aspiration hazard	
No data available	

Delayed and immediate effects as well as chronic effects from short and long-term exposure	
Inhalation of solvent vapours in higher concentration may lead to nausea, headache, drowsiness and dizziness. Repeated and prolonged skin contact may cause removal of natural fat from the skin and irritation of the skin. Eye contact with the product may lead to irritation.	

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish (acute)			
No	Substance name	CAS no.	EC no.
1	ethanol	64-17-5	200-578-6
LC50		8150	mg/l
Duration of exposure		96	h
Species	Leuciscus idus		
Source	Manufacturer		
2	propan-2-ol	67-63-0	200-661-7
LC50		9640	mg/l
Duration of exposure		96	h
Species	Pimephales promelas		
Source	Manufacturer		

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

Toxicity to fish (chronic)	
No data available	

Toxicity to Daphnia (acute)			
No	Substance name	CAS no.	EC no.
1	ethanol	64-17-5	200-578-6
EC50		9268	- 14221
Duration of exposure			48
Species	Daphnia magna		mg/l
Source	Manufacturer		h
2	propan-2-ol	67-63-0	200-661-7
EC50			13299
Duration of exposure			48
Species	Daphnia magna		mg/l
Source	Manufacturer		h

Toxicity to Daphnia (chronic)	
No data available	

Toxicity to algae (acute)			
No	Substance name	CAS no.	EC no.
1	propan-2-ol	67-63-0	200-661-7
EC50			1000
Duration of exposure			72
Species	Desmodesmus subspicatus		mg/l
Source	Manufacturer		h

Toxicity to algae (chronic)	
No data available	

Bacteria toxicity	
No data available	

12.2 Persistence and degradability

Biodegradability			
No	Substance name	CAS no.	EC no.
1	ethanol	64-17-5	200-578-6
Value			%
Source	Manufacturer		
Evaluation	readily biodegradable		
2	propan-2-ol	67-63-0	200-661-7
Value		95	%
Duration		21	day(s)
Method	OECD 301 E		
Source	Manufacturer		
Evaluation	readily biodegradable		

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

No data available.

12.5 Results of PBT and vPvB assessment

No data available.

12.6 Other adverse effects

No data available.

12.7 Other information

Other information
Do not discharge product unmonitored into the environment.

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Residuals must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

SECTION 14: Transport information

14.1 Transport ADR/RID/ADN

Class	3
Classification code	F1
Packing group	II
Hazard identification no.	33
UN number	UN1263
Technical name	PAINT
Special Provision 640	640D
Tunnel restriction code	D/E
Label	3

14.2 Transport IMDG

Class	3
Packing group	II
UN number	UN1263
Proper shipping name	PAINT
EmS	F-E+S-E
Label	3

14.3 Transport ICAO-TI / IATA

Class	3
Packing group	II
UN number	UN1263
Proper shipping name	Paint
Label	3

14.4 Other information

No data available.

14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

14.6 Special precautions for user

No data available.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not relevant

Trade name: edding 366 whiteboard marker (black)

Current version : 2.0.0, issued: 12.01.2016

Replaced version: 1.1.0, issued: 14.03.2012

Region: GB

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

REACH candidate list of substances of very high concern (SVHC) for authorisation

According to available data and the information provided by preliminary suppliers, the product does not contain substances that are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, PREPARATIONS AND ARTICLES

The product is considered being subject to REACH regulation (EC) 1907/2006 annexe XVII.	No 3, 40
---	----------

Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances

This product is subject to Part I of Annex I, risk category:	P5b
--	-----

15.2 Chemical safety assessment

For this mixture a chemical safety assessment has not been carried out.

SECTION 16: Other information

Sources of key data used to compile the data sheet:

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

EC Directives 2000/39/EC, 2006/15/EC, 2009/161/EU

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding chapter.

Department issuing safety data sheet

UMCO Umwelt Consult GmbH

Georg-Wilhelm-Str. 183 , D-21107 Hamburg

Tel.: +49 40 / 79 02 36 300 Fax: +49 40 / 79 02 36 357 e-mail: umco@umco.de

This information is based on our present state of knowledge and experience.

The security data sheet describes products with a view to the security requirements.

However, it should not constitute a guarantee for any specific product properties and shall not establish a legally valid relationship.

Alterations/supplements:

Alterations to the previous edition are marked in the left-hand margin.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO Umwelt Consult GmbH.