


Ampflow A28-400-F24

Specification:


Diameter	77mm (3 in.)
Length	200mm (7.8 in.)
Peak Power	3.2kW (4.3hp)
Stall Torque	25nm (3560 oz-in)
Efficiency	83%
Nominal Voltage	24V
RPM @ 24V	4900
Shaft Diameter	12.7mm (1/2 in.)
Shaft Length	50.8mm (2 in.)
Keyway	3.175mm (1/8 in.)
Magnet Type	Neodymium
No Load Current	4.4
Resistance	0.044Ω
Weight	3.3kg (7.2lbs)

AmpFlow A28-400 24V



Note: Drawing does not show fan

REVISIONS				
ECO	REV	DESCRIPTION	DATE	APPROVED



NOMINAL VOLTAGE: 24
 NO-LOAD RPM: 4900
 MOTOR WEIGHT: 6.9 LBS
 MAGNETS: NEODYMIUM

ITEM	PART NUMBER	DESCRIPTION	QTY
BILL OF MATERIAL			

DO NOT SCALE THIS DRAWING	TOLERANCES UNLESS OTHERWISE NOTED		SIGNATURE	DATE	Powerhouse Engineering A28-400
	2 DEC ±	3 DEC ±	ANGLE ±	DETAIL APP'D	
MATERIAL	THIRD ANGLE PROJECTION		FINISH		SIZE C
DRAWING NUMBER		SCALE 0.900		REV	
DIMENSIONS ARE IN INCHES				SHEET 1 OF 1	