

Order code	Manufacturer code	Description
37-1206	n/a	PLANETRY EPICYCLIC GEARBOX 104:1 (RC)

	Page 1 of 3
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

975D SERIES PLANETARY (EPICYCLIC) METAL GEARBOX (RE 975 MOTOR)



IMPORTANT NOTICE
Due to the wide range of applications for this product it is the users responsibility to establish the products suitability for their individual purpose(s).

RATIOS NOW AVAILABLE AS EX-STOCK ITEMS.

975D41	(4.5v - 15v)	RATIO 4:1
975D1041	(4.5v - 15v)	RATIO 104:1
975D5041	(4.5v - 15v)	RATIO 504:1

Designed for heavy-duty industrial and model applications this robust unit boasts a powerful high quality motor with sintered bronzo bearings. The metal gearbox incorporates sleeved bearings, enabling the high torque transfer from the motor to be transmitted through the gearbox.

MOTOR DATA.

MODEL	VOLTAGE		NO LOAD		MAX EFFICIENCY						STALL TORQUE	
	OPERATING RANGE	NOMINAL	SPEED	CURRENT	SPEED	CURRENT	TORQUE		OUTPUT	EFF	TORQUE	
			R.P.M.	A	R.P.M.	A	oz - in	g - cm	W	%	g - cm	
RE975	6.0 - 12.0	12v CONSTANT	14400	2.0	12255	9.23		599	75.39	68	4200	

REDUCTION TABLE, R.P.M.

SUPPLY VOLTAGE	4.5v	6.0v	9.0v	12.0v	15.0v
975D41	500	1800	2700	3600	
975D1041	19	69	104	138	
975D5041	4	14	21	28	

WEIGHT	
975D41	541g
975D1041	632g
975D5041	683g

RATED TOLERANCE TORQUE (g.cm)	MAX. MOMENTARY TOLERANCE TORQUE
4:1	5000
104:1	20000
504:1	30000

NOTE: To establish Torque Rating in Nm, divide g.cm by 10,197.0


"I'll try" MEX TOLEMAN

MFA/COMO DRILLS

PAGE 2 OF 2

975D SERIES PLANETRY (EPICYCLIC) METAL GEARBOX

GEARBOX DIMENSION:



	Rated Torque Torque @cm	Max momentary Torque @cm	Efficiency %
975D41 (4:1)	5,000	15,000	80
975D1041 (104:1)	20,000	60,000	51
975D5041 (504:1)	30,000	90,000	52

GEARBOX REF.	L
975D41 (4:1)	32.0
975D1041 (104:1)	45.0
975D5041 (504:1)	52.0

FOR ACCESSORIES TO FIT THIS SERIES GEARBOX, REFER TO 919D SERIES PAGE.

ADVANTAGES OF PLANETARY GEARBOXES.

EFFICIENCY:	Efficiencies of planetary gearboxes can be above 90% while some other types of transmission can be 50% or less. This allows the use of smaller motors.
SIZE:	Planetary gearboxes can be half the size of conventional boxes.
WEIGHT:	Weight savings can be as high as 60%, allowing smaller, lighter support structures.
MAINTFNANCE:	Other than routine oil changes, no maintenance is required, eliminating the need to hold spares.
REVERSIBLE:	Planetary gears can be equally efficient in either direction. This is an advantage for use in running machinery in both clockwise and anti-clockwise directions.
COAXIAL:	The coaxial configuration of input and output shafts allows planetary gears to be installed in line with a motor and a machine.

Subject to minimum order quantities of 100 units, the following ratios are also available with a six week lead-time. The physical dimensions of these other gearboxes may vary from the data as illustrated above. Details of individual gearboxes are available upon request.

- | | | |
|-------------------------------|-------------------------------|-------------------------------|
| Gearbox 14 1 with 975 motor | Gearbox 17.1 with 975 motor | Gearbox 24.1 with 975 motor |
| Gearbox 49 1 with 975 motor | Gearbox 61.1 with 975 motor | Gearbox 84.1 with 975 motor |
| Gearbox 144 1 with 975 motor | Gearbox 212.1 with 975 motor | Gearbox 284.1 with 975 motor |
| Gearbox 624 1 with 975 motor | Gearbox 720 1 with 975 motor | Gearbox 864.1 with 975 motor |
| Gearbox 1062 1 with 975 motor | Gearbox 1470 1 with 975 motor | Gearbox 2500.1 with 975 motor |
| Gearbox 3000 1 with 975 motor | Gearbox 3600 1 with 975 motor | |

MFA/COMO DRILLS FELDERLAND LANE, WORTH, DEAL, KENT, CT14 0BT

TEL: 01304 612132. FAX: 01304 614696

E-MAIL: MFA_COMO_DRILL@COMPUSERVE.COM. www.mfacomodrills.com

THE ABOVE FIGURES ARE A GUIDE ONLY AND DO NOT FORM ANY CONTRACTUAL OBLIGATION ON THE PART OF MFA/COMO DRILLS.