

## NSYCVF300M230PF

ClimaSys forced vent. IP54, 300m<sup>3</sup>/h, 230V, with outlet grille and filter G2



### Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter: 300 m <sup>3</sup> /h at 50 Hz Free flow rate with standard filter: 350 m <sup>3</sup> /h at 60 Hz
[Us] rated supply voltage	145...253 V
Input voltage	230 V 50/60 Hz

### Complementary

Power range	36 W 50 Hz 37 W 60 Hz
[In] rated current	0.16 A 60 Hz 0.17 A 50 Hz
Noise level	55...56 dB
Bearing type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External: 116 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.3 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Faston connector
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template 1 power cord
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software

### Environment

#### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

#### Contractual warranty

