

## Tango 49

2G/3G/4G 96mm length panel mount antenna



### Key Features

- Whip style panel mounting
- All 4G frequencies
- 2G and 3G frequency coverage
- 28mm base diameter

### General Description

The Tango 49 is strong slim antenna ideally suited to mounting remotely from the device to maximise signal strength. The antenna can also be mounted directly into alarm/control panels.

The Tango 49 has a wide operating temp between -45°C and 85°C making it extremely versatile for global location.

The antenna can be supplied with alternative cable lengths or connector types for volume orders.

### Additional Considerations

- Extremely versatile for global location
- Strong but slim antenna

## Tango 49

2G/3G/4G 96mm length panel mount antenna


### Key Specifications - Electrical

Temperature range:	-45°C - +75°C
Impedance:	50 Ohm
Gain:	2.16dBi
VSWR:	<2:1
Frequency range:	698 - 960MHz 1710 - 2600 MHz
Polarization:	Vertical

### Key Specifications - Mechanical

Dimensions:	L96 x 28mm Ø
Connector:	SMA
Cable:	RG174
Mounting:	M12 15mm Stud
Max recommended material thickness	7mm

### VSWR



### Ordering Details

Part Number	Description
TANGO49/2.5M/SMAM/17	2G/3G/4G 96mm length panel mount antenna