



Length: 20M
Color: Silver

Material: Aluminum foil
Adhesive power: N/25mm
Tensile strength: N/25mm
Operating temperature: -20°C to 120°C

Product : Aluminum Foil Tape

Structure: Aluminum

Application: Excellent adhesion, commercial grade 90u foil tape. Good for sealing joints / seams against moisture and vapor on foil jacketing insulation. Suitable for many other permanent sealing, holding, splicing or masking applications requiring the protection offered by a foil backing

SAMPLE NAME	Aluminum Foil Tape	SURROUNDING	TEMP22°C RH65%
TEST ITEM	UNIT	RESULT	METHOD
Backing Thickness	MIC	90	
TOTAL THICKNESS	MIC	170	GB/T7125-99
TACK Rolling Ball	CM	20	PSTC-1/ASTM D3330
180°ADHESIVE POWER	N/25MM	26	GB/T2792-98
TENSILE STRENGTH	N/25MM	55	GB/17753-87
ELONGATION	%	3.0	GB/17753-87
Service Temperature	°C	-20~+120	-----
Applying Temperature	°	-5 ~ +40	-----

Color: Silver

Width:75mm \pm 0.5mm

Length:20M \pm 2%M