



RoHS
COMPLIANCE



Features

- ✧ For surface mounted application
- ✧ Easy pick and place
- ✧ Metal to silicon rectifier, majority carrier conduction
- ✧ Low power loss, high efficiency
- ✧ High current capability, low VF
- ✧ High surge current capability
- ✧ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ✧ Epitaxial construction
- ✧ High temperature soldering:
260°C/10 seconds at terminals
- ✧ Green compound with suffix "G" on packing code & prefix "G" on datecode

Mechanical Data

- ✧ Case: JEDEC DO-214AB Molded plastic
- ✧ Terminals: Pure tin plated, lead free
- ✧ Polarity: Indicated by cathode band
- ✧ Packaging: 16mm tape per EIA Std RS-481
- ✧ Weight: 0.21 gram

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.


Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	SS 32	SS 33	SS 34	SS 35	SS 36	SS 39	SS 310	SS 315	SS 320	Unit
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	90	100	150	200	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	63	70	105	140	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	90	100	150	200	V
Maximum Average Forward Rectified Current	I _{F(AV)}	3									A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	100				70					A
Maximum Instantaneous Forward Voltage (Note 1) @ 3 A T _A =25°C T _A =100°C	V _F	0.5 0.4		0.75 0.65		0.85 0.70		0.95 0.80		V	
Maximum Reverse Current @ Rated VR T _A =25°C T _A =100°C T _A =125°C	I _R	0.5					0.1				mA
		10			5		-				
		-					0.5				
Typical Thermal Resistance	R _{θJL} R _{θJA}	17 55									°C/W
Operating Temperature Range	T _J	- 55 to + 125				- 55 to + 150					°C
Storage Temperature Range	T _{STG}	- 55 to + 150									°C

Note 1: Pluse Test with PW=300 usec, 1% Duty Cycle

SS32 - SS320 3.0AMPS Surface Mount Schottky Barrier Rectifiers SMC/DO-214AB



Dimensions in inches and (millimeters)



Marking Diagram

SS3X = Specific Device Code
G = Green Compound
Y = Year
M = Work Month

RATINGS AND CHARACTERISTIC CURVES (SS32 THRU SS320)

FIG. 1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE




FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE

