


CAT.6 12 PORT VERTICAL PATCH PANEL (FTP)

REVISION RECORD			
REV.	CONTENT	MOD.	DATE
01	NEW PUBLISHING		





Performance:
Meets Cat.6 EIA/TIA568B.2-1 Standard.

Materials:
Bottom Panel: 1.5mm thickness Metallic Panel(SECC)/RAL7035
Upper Panel Cover: 1.0mm thickness Metallic Panel(SECC)/RAL7035
RJ45 Jack Shielded Case: 0.25mm thickness Brass with Ni plated
RJ45 Jack Housing: Fireproof PBT UL-94V0
RJ45 Jack Insert: Housing-Fireproof PBT UL-94V0
Contact-8P8C Phosphor bronze with 3 to 50 u" gold plated
PCB: FR-4/1.6mm UL-94V0
IDC: Body- Fireproof ABS UL-94V0
Pin: Phosphor Bronze & Tinned
Label Color Code: T568 A/B
IDC Terminal: For 22-26 AWG Cable


Electrical Specifications:
Insulation Resistance: 500M ohms (min.)
Contact Resistance: 20m ohms (max.)
Current Rating: 1.5 Amps.
DC Resistance: 0.1 ohms(max.)
Withstanding Voltage: 1000 VAC RMS @ 60Hz/ 1 min.

Accessory:
1.M3 Screw Set, For Pre-Assembled Ground Wire
2.Cable Tie(60X2.5mm)X12Pcs
3.Instruction Sheet

Mechanical Specifications:
IDC Punch Down Cycle: Over 25 Cycles (min.)
RJ45 Jack Insertion Cycle: Over 200 Cycles (min.)



IDC:



0.	CAT. 6 PATCH PANEL	NP0041	1			
NO.	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES	
DES.	HF	DATE	08/09/15	UNITS	mm	FIRST ANGLE PROJECTION
CHK.		DATE		SIZE	A4	
APP.		DATE		SCALE	2:3	DWG NO.
LogiLink®					TITLE	CAT. 6 PATCH PANEL
						1 of 1