


U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SILVYN® BRAID PA6	12.09.2012

Protection against dust
 Abrasion protection
 Cut into length without frizzle on the conduit's end
 Simple, fast cable bundling
 Can be cut without the need for a thermo-cutting tool



Info

NEW!!!

Cut into length without frizzle on the conduit's end
 Saves time

Application range

Easy cable protection
 Additional insulation
 Bundling and guiding of cables and wires
 Low rodent-protection

Design

Polyamide 6.6 - halogen-free

Product features

Abrasion-resistant
 Flexible
 Can be cut at cold temperatures

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

On request:

Bulk containers on rolls

Note:

Halogen and cadmium-free
 Self-extinguishing according to DIN 75200/FMVSS302 and
 DIN5510

Colour delivered:

Black (RAL 9005), UV-resistant

Material:


Polyamide 6.6 - halogen-free

Temperature range:

-55°C to +125°C

Product Management	Document: LAPP_PRO206305EN.pdf	1 / 3
--------------------	--------------------------------	-------

Part number	Clamping range (mm)	PU (m)
SILVYN BRAID PA6		
61721260	4 - 10	20.0
61721261	10 - 14	15.0
61721262	14 - 24	15.0
61721263	14 - 24	10.0
61721264	18 - 26	10.0
61721265	32 - 44	5.0

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SILVYN® BRAID PA6	12.09.2012



Product Management	Document: LAPP_PRO206305EN.pdf	3 / 3
--------------------	--------------------------------	-------