

## Push button Ø 19 mm silver contact

82-5572.1000



<https://www.eao.com/component/82-5572.1000/en...>

Your product:

---



82-5572.1000

Push button Ø 19 mm silver contact

#### FRONT

**Front dimension:** Ø 22 mm

**Front form:** Round

**Front bezel material:** Aluminium

**Front bezel shape:** Flush

#### MOUNTING

**Mounting cut-out:** Ø 19 mm

**Mounting type:** Panel mounting

#### OPERATING-/INDICATION PART

**Lens colour:** Nature

**Lens material:** Aluminium

**Lens illumination:** Non illuminated

**Lens shape:** Convex

**Lens optics:** opaque

#### ELECTRICAL CHARACTERISTICS

**Switching voltage and switching current:**

according to IEC 60947-5-1 (Silver contacts)

Service categorie AC-15

Voltage

24 VAC

35 VAC

110 VAC

220 VAC

Current

1 A

1 A (M12 version)

1 A

0.5 A

Switch rating DC service categorie DC-13 (Silver contacts)

Voltage

24 VDC

35 VDC

110 VDC

220 VDC

Current

0.7 A

0.5 A (M12 version)

0.2 A

0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$  0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

|                                                    |                                                            |
|----------------------------------------------------|------------------------------------------------------------|
| <b>Contacts:</b>                                   | 1 C                                                        |
| <b>Rated Operational Voltage <math>U_e</math>:</b> | 250 VAC                                                    |
| <b>Rated insulation voltage <math>U_i</math>:</b>  | 250 V                                                      |
| <b>Switching rating:</b>                           | 240 V                                                      |
| <b>Electrical lifetime:</b>                        | 50 000 cycles of operation                                 |
| <b>Electric strength:</b>                          | 1500 VAC, 50 Hz 1 minute between life terminals and ground |
| <b>Pollution degree:</b>                           | 2, according to EN IEC 60947-1                             |
| <b>Thermal current <math>I_{th}</math>:</b>        | 5 A                                                        |

## MECHANICAL CHARACTERISTICS

|                             |                                       |
|-----------------------------|---------------------------------------|
| <b>Terminal:</b>            | Screw terminal                        |
| <b>Contact material:</b>    | Silver                                |
| <b>Switching action:</b>    | Momentary                             |
| <b>Switching system:</b>    | Snap-action switching element         |
| <b>Mechanical lifetime:</b> | 1 Mil. cycles of operation            |
| <b>Operating force:</b>     | 4 N ... 7 N                           |
| <b>Operating Travel:</b>    | ca. 3 mm                              |
| <b>Tightening torque:</b>   | 0.5 ... 0.6 Nm, Screw terminal 0.1 Nm |
| <b>Weight:</b>              | 0.019 kg                              |

## AMBIENT CONDITION

**IP front protection:**

IP65, IP67

**Operating temperature:**

– 30 °C ... + 70 °C

**Storage temperature:**

– 40 °C ... + 80 °C

**Shock resistance:**

Max. 500 m / s<sup>2</sup> as per IEC 60068-2-27

**Vibration resistance:**

10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

**Climate resistance:**

Damp heat, 21 days according to IEC 60512-11

**CERTIFICATE**

**Approbations:**

CB, CCC, C UL, UL

**Conformities:**

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

**REACH:**

REACH compliant

**RoHS:**


RoHS compliant

**OTHER**


**Short Description:**

Push button Ø 19 mm silver contact, Momentary, 240 V, 1 C, Screw terminal, Round, Aluminium, Nature


**Wiring diagrams:**




**Component layouts:**



### Mounting cut-outs:



### Dimension drawings:



A = Solder terminal  
B = Screw terminal