

U.I. Lapp GmbH	PRODUCT INFORMATION	
		12.09.2012

Reliable bending protection for cable conservation and functional reliability
 Save up to 70% of the time with the innovative CLICK system
 No thread required
 To protect flexible cables
 Fewer parts, counter nut no longer needed



Good chemical resistance



Heat-resistant




Mechanical resistance



Assembly time



Space requirement



Acid-resistant



Variety of approval certifications

Info

The most innovative cable insertion system in the market for a fast and highly flexible assembly. Simply click in - turn to the left - turn to the right - finished. The result: fixed, centred, strain-relieved fitting and maximum protection class in a few seconds.

Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Robotics industry

Moving machine parts

Apparatus construction

Light and sound applications

Norm references / Approvals

UL File Nr. E79903

Included

Included: disassembly tool

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: LAPP_PRO115371EN.pdf	1 / 4
--------------------	--------------------------------	-------

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
		12.09.2012


Technical Data

Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Body: special polyamide Seal: special elastomer
Protection rating:	IP 68 - 4 bar (M12) IP 68 - 5 bar (M16 - M32)
Temperature range:	-20°C to +100°C

Product Management	Document: LAPP_PRO115371EN.pdf	2 / 4
--------------------	--------------------------------	-------

Part number	Article designation / size	Clamping range ØF (mm)	M (hole in mm)	SW1/SW2 mm	Overall length/ C (mm)	Thread length/ D (mm)	Wall thickness/ S (mm)	Pieces / PU
SKINTOP® CLICK BS light grey								
53112932	CLICK BS 12	3,5-7	12.3 (-0.2)	18 / 15	74.0	8.0	1 - 4	50
53112888	CLICK BS 16	5-9	16.3 (-0.2)	22 / 19	94.0	8.0	1 - 4	50
53112889	CLICK BS 20	7-13	20.3 (-0.2)	27 / 25	108.0	8.0	1 - 4	25
53112890	CLICK BS 25	9-17	25.3 (-0.2)	32 / 30	127.0	8.0	1 - 4	25
53112933	CLICK BS 32	11-21	32.3 (-0.2)	40 / 36	155.0	8.0	1 - 4	25
SKINTOP® CLICK BS silver grey								
53112934	CLICK BS 12	3,5-7	12.3 (-0.2)	18 / 15	74.0	8.0	1 - 4	50
53112906	CLICK BS 16	5-9	16.3 (-0.2)	22 / 25	94.0	8.0	1 - 4	50
53112907	CLICK BS 20	7-13	20.3 (-0.2)	27 / 25	108.0	8.0	1 - 4	25
53112908	CLICK BS 25	9-17	25.3 (-0.2)	32 / 30	127.0	8.0	1 - 4	25
53112935	CLICK BS 32	11-21	32.3 (-0.2)	40 / 36	155.0	8.0	1 - 4	25
SKINTOP® CLICK BS black								
53112936	CLICK BS 12	3,5-7	12.3 (-0.2)	18 / 15	74.0	8.0	1 - 4	50
53112909	CLICK BS 16	5-9	16.3 (-0.2)	22 / 19	94.0	8.0	1 - 4	50
53112911	CLICK BS 20	7-13	20.3 (-0.2)	27 / 25	108.0	8.0	1 - 4	25
53112912	CLICK BS 25	9-17	25.3 (-0.2)	32 / 30	127.0	8.0	1 - 4	25
53112937	CLICK BS 32	11-21	32.3 (-0.2)	40 / 36	155.0	8.0	1 - 4	25

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
		12.09.2012



Product Management	Document: LAPP_PRO115371EN.pdf	4 / 4
--------------------	--------------------------------	-------