

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® MS-M-XL	12.09.2012

Especially for thick walls
Maximum reliability
Optimum strain relief
Wide, variable clamping ranges



Application range

With long connection thread for applications involving a thicker wall.

Design

Metric connection thread acc. to EN 50262

Approvals (Norm references)

UL File Nr. E79903

Note

Counter nut to be used: SKINDICHT® SM-M

Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:

Refer to Appendix T21 for the installation dimensions and torques

Material:

Body: nickel-plated brass
Insert: polyamide
Sealing ring: CR
O-ring: NBR

Protection rating:

Remark: A RoHS-non-compliant version is marketed under ÖLFLEX® 110 with VDE-REG.-Nr. 8067. To order this, please add appendix <1> to the below stated part numbers. This does not affect the above given further technical data or description.
IP 69 K
IP 68 - 10 bar

Temperature range:


Dynamic: -30 °C to +100 °C
Fixed: -40 °C to +100 °C



Product Management	Document: LAPP_PRO988EN.pdf	1 / 3
--------------------	-----------------------------	-------

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
SKINTOP® MS-M-XL						
53112005	12 x 1,5	3-7	16	32,8	12.0	100
53112015	16 x 1,5	4,5-10	20	37.0	12.0	50
53112025	20 x 1,5	7-13	24	39,5	12.0	50
53112035	25 x 1,5	9-17	29	41,5	12.0	25
53112045	32 x 1,5	11-21	36	48,2	15.0	25
53112055	40 x 1,5	19-28	45	53,5	15.0	10
53112065	50 x 1,5	27-35	54	57.0	15.0	5

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINTOP® MS-M-XL	12.09.2012



Product Management	Document: LAPP_PRO988EN.pdf	3 / 3
--------------------	-----------------------------	-------