

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINDICHT® SH	12.09.2012

Seawater-resistant
Anti-magnetic
Corrosion-resistant
Stable and safe strain relief



Application range

Extremely robust and solid strain relief cable gland.
Building sites
Plant engineering
Electric motor manufacturing

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:

The installation dimensions
can be found in appendix T21

On request:

Available with long connection thread

Material:

Body: nickel-plated brass

Protection rating:


IP 20



Product Management	Document: LAPP_PRO1085EN.pdf	1 / 3
--------------------	------------------------------	-------

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Max. fitting size for installation (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINDICHT® SH							
52000830	SH 7	8 - 10	15	22	17,5	5.5	50
52000840	SH 9	10 - 12,5	17	25	20,5	6.0	50
52000850	SH 11	11 - 15	20	28	21,5	6.0	50
52000860	SH 13,5	14 - 16,5	22	32	24.0	7.5	25
52000870	SH 16	15 - 18	24	35	26.0	7.5	25
52000880	SH 21	18 - 23,5	30	46	29.0	8.0	25
52000890	SH 29	23 - 31	41	58	33.0	8.0	10
52000900	SH 36	29 - 40,5	50	70	36,5	9.5	10
52000910	SH 42	34 - 45	57	78	38.0	10.0	5
52000920	SH 48	39 - 50	64	86	39,5	11.5	5

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINDICHT® SH	12.09.2012



Product Management	Document: LAPP_PRO1085EN.pdf	3 / 3
--------------------	------------------------------	-------