

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® KR-M ATEX plus	12.09.2012

For the benefits, refer to SKINTOP® K-M ATEX plus



Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	IBExU08ATEX 1063 X Ex II 1D Ex tD A20 IP 6x Ex II 2G Ex e II
Colour delivered:	RAL 9005 black/UV-resistant
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	Remark: A RoHS-non-compliant version is marketed under ÖLFLEX® 110 with VDE-REG.-Nr. 8067. To order this, please add appendix <1> to the below stated part numbers. This does not affect the above given further technical data or description.
Temperature range:	-20°C to +80°C

Product Management	Document: LAPP_PRO982EN.pdf	1 / 2
--------------------	-----------------------------	-------



SKINTOP® KR-M ATEX plus

12.09.2012

Part number	Article designation / size	Clamping range ØF (mm)	Thread M	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)
SKINTOP® KR-M ATEX plus						
54115205	KR-M 12 ATEX plus	2-4	12 x 1.5	15	26,5 - 30	8.0
54115215	KR-M 16 ATEX plus	4-6	16 x 1.5	19	29 - 34	8.0
54115225	KR-M 20 ATEX plus	5-10	20 x 1.5	25	34 - 37	9.0
54115235	KR-M 25 ATEX plus	6-13	25 x 1.5	30	35 - 40	10.0
54115245	KR-M 32 ATEX plus	9-15	32 x 1.5	36	39 - 47	10.0
54115255	KR-M 40 ATEX plus	16-23	40 x 1.5	46	43 - 52	10.0
54115265	KR-M 50 ATEX plus	22-29	50 x 1.5	55	54 - 62	12.0
54115275	KR-M 63 ATEX plus	29-39	63 x 1.5	66	59 - 71	12.0