


Technical data sheet

Article number:
170-00060

HEGPX06



Product Group	High-expansion polyester braided sleeving
Product Family	Helagaine HEGPX
Material	Polyester (PET)
Colour	Black (BK)
Application Method	By hot-cutting the sleeving, the yarn is melted and fused, thereby preventing fraying.
Application Range	Indoor Use
Bundle Ø max.	9 mm
Bundle Ø min.	3 mm
Melting Point	+250 °C
Operating Temperature	-50 °C to +150 °C
Package Content	200 m
Package Content packed in	meter
Specifications	EN 45545-2
UL-File Number	E197993

HF ✓ RoHS ✓

EN 45545-2 