

## Product information

**97 33 01**

### KNIPEX MultiCrimp®

Lever Action Crimping Pliers with changer magazine














- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Chrome vanadium electric steel in special quality, oil-hardened
- Round magazine: plastic, fibreglass-reinforced



#### General

|             |                            |
|-------------|----------------------------|
| Article No. | 97 33 01                   |
| EAN         | 4003773066927              |
| Pliers      | burnished                  |
| Handles     | with multi-component grips |
| weight      | 770 g                      |
| Dimensions  | 250 x 75 x 28 mm           |
| Reach       | yes                        |
| RohS        | no                         |

#### Technical details

|  |   |
|--|---|
|     |   |
| Applications   | non-insulated open plug type connectors (plug width 4.8 + 6.3 mm) |
| Capacity in square millimetres   | 0.5 — 6.0 mm <sup>2</sup>   |
| Number of crimping positions   | 3   |
| AWG  | 20 — 10   |
|       |   |
| Applications   | insulated terminals, plug connectors + butt connectors            |
| Capacity in square millimetres   | 0.5 — 6.0 mm <sup>2</sup>   |
| Number of crimping positions   | 3   |
| AWG  | 20 — 10   |
|        |   |
| Applications   | Wire ferrules   |
| Capacity in square millimetres   | 0.25 — 6.0 mm <sup>2</sup>  |
| Number of crimping positions   | 5   |
| AWG  | 24 — 10   |

## Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| ETIM 5.0       | EC000168   |
| ETIM 6.0       | EC000168   |
| proficl@ss 6.0 | AAA946c003 |
| UNSPSC 13.1    | 27112147   |

## Accessories

|            |  |
|------------|--|
| 97 39 05   | Crimping dies<br>for non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)   |
| 97 39 09   | Crimping dies<br>for insulated and non-insulated wire ferrules   |
| 97 39 13 A | Crimping dies<br>for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267 |
| 97 39 06   | Crimping dies<br>for insulated terminals, plug connectors and butt connectors  |
| 97 39 08   | Crimping dies<br>for insulated and non-insulated wire ferrules   |
| 97 39 13   | Crimping dies<br>for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267 |
| 97 39 90   | Changer magazine<br>empty  |

*technical change and errors excepted*



Changing the crimping dies: unlock the magazine position, take out the set of dies which the pliers have been pushed on



Changing position: service lever opens out for parallel jaw positioning



Fold in the service lever and press the pliers – ready for use again

