

## Product information

# 71 82 950

## Concrete Mesh Cutter



- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock-absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
- Joint: special tool steel, forged
- Handles: steel tube, powder-coated
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

### General

Article No.	71 82 950
EAN	4003773066798
Head	grey afromentized
Handles	with multi-component grips
weight	4,110 g
Dimensions	950 x 180 x 40 mm
Reach	no
RohS	no

### Technical details

HRC 19	Ø 11 mm
HRC 48	Ø 6 mm
HRC 40	Ø 9 mm
Cutting edge length mm	44 mm
Head thickness	40 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	23151901

*technical change and errors excepted*



The special shape of the mesh cutter head, 71 82 950, enables it to cut structural steel that is lying down flat



