

Product information

97 52 04

Crimping Pliers

Also for two-hand operation




- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 52 04
EAN	4003773025450
Pliers	burnished
Head	burnished
Handles	with non-slip plastic grips
weight	562 g
Dimensions	250 x 82 x 27 mm
Reach	yes
RohS	no

Technical details



Applications	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 2.5 mm ²
Number of crimping positions	4
AWG	26 — 14

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147


Accessories

97 49 94	Locator for 97 49 04
----------	----------------------

technical change and errors excepted



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm², two-hand operation is possible by the longer handles



Second step: now use the whole hand for further crimping procedure



First step: move the handle with two fingers only until both jaws touch the connector to be crimped