

Product information

95 17 200

Cable Shears

With twin cutting edge

IEC 60900 DIN EN 60900

⚠ 1000 V

- For cutting copper and aluminium cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- By dividing the cutting actions into initial cut (insulating sheath in the front cutting area) and final cut (conductor in the back cutting area), cables up to Ø 20 mm can be cut in one-hand operation
- Low handforce required due to favourable lever ratio and special blade geometry
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

General

Article No.	95 17 200
EAN	4003773026952
Shears	chrome plated
Handles	with dipped insulation, VDE-tested
weight	360 g
Dimensions	200 x 80 x 34 mm
Standard	DIN EN 60900 IEC 60900
Reach	Nein
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	70 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 20 mm
AWG	2 / 0
VDE tested	yes

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted



Final cut: after cutting the sheath in the front profile the conductors in the rear part are cut. Initial cut in the front profile, final cut in the rear profile - to keep it as easy as possible.



Initial cut: using the front cutting edge to cut the insulating sheath on larger cable diameters leaves an ergonomic handle opening width.