

Product information

97 52 10

Crimping Pliers

Also for two-hand operation




- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 52 10
EAN	4003773023678
Pliers	burnished
Head	burnished
Handles	with non-slip plastic grips
weight	577 g
Dimensions	250 x 81 x 24 mm
Reach	yes
RohS	no

Technical details



Applications	Coax-, BNC- and TNC-connectors
Number of crimping positions	3
	5.4 mm / 6.48 mm / 1.72 mm
Sleeves (diameter)	Ø 6.4 / 7.6 / 2.1 mm
Cable type	RG 58 / 59 / 62 / 71 / 223

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm², two-hand operation is possible by the longer handles



Second step: now use the whole hand for further crimping procedure



First step: move the handle with two fingers only until both jaws touch the connector to be crimped