

Product information

77 22 130

Electronics Diagonal Cutter

DIN ISO 9654




- Round head, with small bevel
- Cutting edge hardness approx. 60 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened



General	
Article No.	77 22 130
EAN	4003773040446
Head	mirror polished
Handles	with multi-component grips
weight	124 g
Dimensions	130 x 49 x 18 mm
Standard	DIN ISO 9654
Reach	no
RohS	no

Technical details	
Style	2
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 2 mm
	18 mm
	9 mm
Head width (A)	15 mm





Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted