

Product information

97 53 14

Self-Adjusting Crimping Pliers for wire ferrules


With lateral access



- Narrow handle width and improved ergonomics
- Expanded capacity of hexagonal crimping up to 10 mm²
- Hexagonal compression for confined connection dimensions
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened



| General | |
|-------------|----------------------------|
| Article No. | 97 53 14 |
| EAN | 4003773041474 |
| Pliers | burnished |
| Handles | with multi-component grips |
| weight | 445 g |
| Dimensions | 180 x 75 x 21 mm |
| Reach | yes |
| RohS | no |

| Technical details | |
|--|---------------------------|
|  | |
| Applications | Wire ferrules |
| Capacity in square millimetres | 0.08 — 10 mm ² |
| Number of crimping positions | 1 |
| AWG | 28 — 8 |

| Classification | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000168 |
| ETIM 6.0 | EC000168 |
| proficl@ss 6.0 | AAA946c003 |
| UNSPSC 13.1 | 27112147 |

technical change and errors excepted